

, WO60



Connection terminal, 3 pole without cover.

INDUSTRY STANDARDS

UL

CSA

GL

FEATURES

Description: Connection set, 3-pole without cover cap.

Rated voltage: 690 V

Width: 153

Pack quantity: 1 pc.

Approvals: CSA, UL, GL

SPECIFICATIONS

Table 1/1						
Catalog Number	Высота мм	Ширина мм	Глубина мм	Material	Finish	Color
01537	100mm	153mm	25mm	Сталь	Powder Coated	Light Gray
01538	100mm	153mm	25mm	Сталь	Powder Coated	Light Gray

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE