

, DIPH



The DIPH profile system is a 40 mm wide and 25 mm high profile to be mounted on the sides and base of HDW range enclosures. It has two rows of hole patterns and can be used in combination with the CLPK and CLPF profiles. No machining is required.

FEATURES

Description: The DIPH profile system is a 40 mm wide and 25 mm high profile to be mounted on the sides and base of HDW range enclosures. It has two rows of hole patterns and can be used in combination with the CLPK and CLPF profiles. No machining is required.

Pack quantity: 4 profiles including fixing accessories.

Material: Zinc plated Steel.

SPECIFICATIONS

Material: Сталь
Finish: Zinc Plated

Table 1/1						
Catalog Number	Высота мм	Ширина мм	Глубина мм	Load Rating	Enclosure Material	Quick Ship
DIPH210	25mm	40mm	210mm	150N	Нержавеющая сталь	No
DIPH300	25mm	40mm	300mm	150N	Нержавеющая сталь	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE