

Cable Entry Gland Plate Blind Cover, CEAB, 55x126x12mm 8, Blk, Plastic

CATALOG NUMBER

CEAB816



Blind cover-to-cover opening for CEP and CCF cable entries.

INDUSTRY STANDARDS

UL94 V-0 Flammability; File No. E61997

NEMA Type 1, 12, 4X (indoor only)

CE

IP66

FEATURES

Description: Blind cover-to-cover openings for CEP and CCF cable entries. Mounted over the opening by using screw fixation.

Finish: Black

Flammability: UL94 V-0

Material: Polyamide 6.6 / TPE

Pack quantity: 10 pcs

Protection: IP66

Temperature resistance: -40°C to +120°C

PRODUCT ATTRIBUTES

Высота мм: 55mm

Ширина мм: 126mm

Глубина мм: 11.5mm

Product Family: организация укладки кабелей

Material: Plastic

Finish: Необработанные

Color: Черный

Operating Temperature: -40 to 120°C

Weight: 0.0426303854875283kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE