

, ADI



Displays and indicators can be mounted on a surface within the enclosure while covering other components, and preventing unauthorized access.

FEATURES

Description: For controls, meters, lamps, etc. Hinges can be mounted to allow left or right hand opening. Lock double-bit 3 mm insert; 700 mm high doors and above have 2 locks. Usable depth between inner and external door: 35 mm. Adjustable depth position with AMG accessory. Workable area: H-55, W- 108. 19" version available on request. Machining is required for stainless steel enclosures.

Material: Door 1.5 mm mild steel, vertical top and bottom profiles 2 mm mild steel.

Finish: RAL 7035 structured powder coating.

Protection: IP 2XC.

Pack quantity: Inner door, two vertical profiles, top and bottom profiles and mounting accessories.

SPECIFICATIONS

Thickness: 1.5mm
Color: Light Gray
Material: Mild Steel
Finish: Powder Coated
Color Code: RAL 7035

Table 1/1

Catalog Number	Высота мм	Ширина мм	Глубина мм	Door Size	Latch Quantity	Enclosure Material
ADI04030R5	374mm	261mm	71mm	345 x 192mm	1	Mild Steel
ADI04040R5	374mm	374mm	71mm	345 x 292mm	1	Mild Steel
ADI04050R5	374mm	461mm	71mm	345 x 392mm	1	Mild Steel
ADI04060R5	374mm	561mm	71mm	345 x 492mm	1	Mild Steel
ADI05030R5	474mm	261mm	71mm	445 x 192mm	1	Mild Steel
ADI05040R5	474mm	374mm	71mm	445 x 292mm	1	Mild Steel
ADI05050R5	474mm	461mm	71mm	445 x 392mm	1	Mild Steel
ADI06040R5	574mm	374mm	71mm	545 x 292mm	1	Mild Steel
ADI06050R5	574mm	461mm	71mm	545 x 392mm	1	Mild Steel
ADI06060R5	574mm	561mm	71mm	545 x 492mm	1	Mild Steel
ADI06080R5	574mm	761mm	71mm	545 x 692mm	1	Mild Steel
ADI07050R5	674mm	461mm	71mm	645 x 392mm	2	Mild Steel
ADI08040R5	774mm	374mm	71mm	745 x 292mm	2	Mild Steel
ADI08060R5	774mm	561mm	71mm	745 x 492mm	2	Mild Steel
ADI08080R5	774mm	761mm	71mm	745 x 692mm	2	Mild Steel
ADI10060R5	974mm	561mm	71mm	945 x 492mm	2	Mild Steel

Catalog Number	Высота мм	Ширина мм	Глубина мм	Door Size	Latch Quantity	EnclosureMaterial
ADI10080R5	974mm	761mm	71mm	945 x 692mm	2	Mild Steel
ADI12060R5	1174mm	561mm	71mm	1145 x 492mm	2	Mild Steel
ADI12080R5	1174mm	761mm	71mm	1145 x 692mm	2	Mild Steel

ADDITIONAL PRODUCT DETAILS

Not suitable for AFS.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE