

, LF

These adjustable feet allow the enclosure to be levelled and adjusted in height up to 30 mm, if required.



FEATURES

Description: Adjustable feet for leveling enclosures placed on uneven ground. Mounted directly to the enclosure's frame.
Adjustment stroke: 30 mm.

Maximum load: 3000 N per foot.

Pack quantity: 4 pieces with mounting accessories.

SPECIFICATIONS

Table 1/1						
Catalog Number	Высота мм	Ширина мм	Глубина мм	Enclosure Material	Product Family	Material
LF430	67mm	48mm	48mm	Mild Steel	Free-Standing	Plastic, Plastic

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE