

, DPM



This glazed partial door creates a practical solution for a computer screen to be mounted within an enclosure. The door keeps the computer screen safe from theft and environmental hazards.

FEATURES

Description: For monitor size 14"-21". Used in combination with the hinged keyboard tray DPK, allows the installation of a PC in any floor standing enclosures. The remaining space will be filled with top and bottom panels DPC and partial doors DP.

Material: 1.75 mm steel plate, viewing area: 4 mm safety glass.

Finish: RAL 7035 structured powder coating.

Protection: Complies with IP 44.

Pack quantity: 1 door with hinges and double-bit 3 mm lock.

Mounting requirements: To be used in combination with keyboard tray DPK. Recommended in combination with CDH to avoid a gap between the above/below panels.

SPECIFICATIONS

Color: Light Gray
Material: Mild Steel
Finish: Powder Coated
Color Code: RAL 7035

Table 1/1						
Catalog Number	Высота мм	Ширина мм	Глубина мм	Latch Quantity	Window Size	Enclosure Material
DPM0506R5	500mm	600mm	17mm	2	360 x 455mm	Mild Steel
DPM0606R5	600mm	600mm	17mm	2	460 x 455mm	Mild Steel

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE