

, ASST



A stainless steel rain hood provides shelter via a sloped roof and protects installed components from accumulated water dripping into the enclosure when the door is opened.

FEATURES

Description: To be fitted as an outdoor shelter on stainless steel wall mounted enclosures. The roof is slightly sloped and has a drip strip. Machining is required. Dimensions of the enclosure will be increased by H: 60 mm, W: 20 mm and D: 20 mm

Material: AISI 304 / AISI 316L pre-grained stainless steel

Finish: 400 pre-grained stainless steel

Pack quantity: 1 rain hood with mounting material

Additional information: ASST is not compatible with 180° MMHS hinges

SPECIFICATIONS

Finish: Brushed

Table 1/1

Catalog Number	Высота мм	Ширина мм	Глубина мм	Material	Enclosure Material	Product Family
ASST103	59mm	1000mm	300mm	Stainless Steel 304	Mild Steel	Wall Mounted
ASST103-316	59mm	1000mm	300mm	Stainless Steel 316L	Mild Steel	Wall Mounted
ASST123	59mm	1200mm	300mm	Stainless Steel 304	Mild Steel	Wall Mounted
ASST123-316	59mm	1200mm	300mm	Stainless Steel 316L	Mild Steel	Wall Mounted
ASST124	59mm	1200mm	400mm	Stainless Steel 304	Mild Steel	Wall Mounted
ASST124-316	59mm	1200mm	400mm	Stainless Steel 316L	Mild Steel	Wall Mounted
ASST042	59mm	400mm	210mm	Stainless Steel 304	Mild Steel	Wall Mounted
ASST042-316	59mm	400mm	210mm	Stainless Steel 316L	Mild Steel	Wall Mounted
ASST062	59mm	600mm	210mm	Stainless Steel 304	Mild Steel	Wall Mounted
ASST062-316	59mm	600mm	210mm	Stainless Steel 316L	Mild Steel	Wall Mounted
ASST063	59mm	600mm	300mm	Stainless Steel 304	Mild Steel	Wall Mounted
ASST063-316	59mm	600mm	300mm	Stainless Steel 316L	Mild Steel	Wall Mounted
ASST083	59mm	800mm	300mm	Stainless Steel 304	Mild Steel	Wall Mounted
ASST083-316	59mm	800mm	300mm	Stainless Steel 316L	Mild Steel	Wall Mounted
ASST084	59mm	800mm	400mm	Stainless Steel 304	Mild Steel	Wall Mounted
ASST084-316	59mm	800mm	400mm	Stainless Steel 316L	Mild Steel	Wall Mounted

ADDITIONAL PRODUCT DETAILS

Not suitable for AFS.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE