

Front Panel, Front Anodized, Rear Conductive, Unshielded

Power Utilities

Front panel, unshielded, front anodized and rear conductive.



CERTIFICATIONS



FEATURES

Partial width front panel, Al, 2.5 mm

Al, front anodized, conductive

SPECIFICATIONS

Table 1/3

Catalog Number	Rack Height	Rack Width	Package Quantity	Handle Type	Mounting	Front Finish
30847-469	5 U	84 HP	1	Her	Screw-on Front	Anodized
30847-467	5 U	42 HP	1	Her	Screw-on Front	Anodized

CatalogNumber	Rack Height	Rack Width	Package Quantity	Handle Type	Mounting	Front Finish
30847-460	2 U	63 HP	1	Her	Screw-on Front	Anodized
30847-461	2 U	84 HP	1	Her	Screw-on Front	Anodized
30838-162	6 U	42 HP	1	Her	Screw-on Front	Anodized
30847-459	2 U	42 HP	1	Her	Screw-on Front	Anodized
30847-464	4 U	63 HP	1	Her	Screw-on Front	Anodized
30838-123	3 U	84 HP	1	Her	Screw-on Front	Anodized
30838-183	6 U	63 HP	1	Her	Screw-on Front	Anodized
30838-102	3 U	63 HP	1	Her	Screw-on Front	Anodized
30847-465	4 U	84 HP	1	Her	Screw-on Front	Anodized
30838-204	6 U	84 HP	1	Her	Screw-on Front	Anodized
30838-081	3 U	42 HP	1	Her	Screw-on Front	Anodized
30847-468	5 U	63 HP	1	Her	Screw-on Front	Anodized
30847-463	4 U	42 HP	1	Her	Screw-on Front	Anodized
30847-458	2 U	28 HP	5	Her	Screw-on Front	Anodized
30847-470	3 U	2 HP	5	Her	Screw-on Front	Anodized
30838-053	3 U	14 HP	5	Her	Screw-on Front	Anodized
30838-067	3 U	28 HP	5	Her	Screw-on Front	Anodized
30838-051	3 U	12 HP	5	Her	Screw-on Front	Anodized

CatalogNumber	Rack Height	Rack Width	Package Quantity	Handle Type	Mounting	Front Finish
30838-045	3 U	6 HP	5	Her	Screw-on Front	Anodized
30838-046	3 U	7 HP	5	Her	Screw-on Front	Anodized
30847-471	3 U	3 HP	5	Her	Screw-on Front	Anodized
30838-044	3 U	5 HP	5	Her	Screw-on Front	Anodized
30838-055	3 U	16 HP		Her	Screw-on Front	Anodized
30838-043	3 U	4 HP	5	Her	Screw-on Front	Anodized
30838-049	3 U	10 HP	5	Her	Screw-on Front	Anodized
30838-060	3 U	21 HP	5	Her	Screw-on Front	Anodized
30838-047	3 U	8 HP	5	Her	Screw-on Front	Anodized
30847-476	4 U	4 HP	5		Screw-on Front	Anodized
30847-462	4 U	28 HP	5	Her	Screw-on Front	Anodized
30838-124	6 U	4 HP	5	Her	Screw-on Front	Anodized
30847-466	5 U	28 HP	5	Her	Screw-on Front	Anodized
30838-125	6 U	5 HP	5	Her	Screw-on Front	Anodized
30838-130	6 U	10 HP	5	Her	Screw-on Front	Anodized
30838-132	6 U	12 HP	5	Her	Screw-on Front	Anodized
30838-141	6 U	21 HP	5	Her	Screw-on Front	Anodized
30838-134	6 U	14 HP	5	Her	Screw-on Front	Anodized

CatalogNumber	Rack Height	Rack Width	Package Quantity	Handle Type	Mounting	Front Finish
30838-136	6 U	16 HP	5	Нет	Screw-on Front	Anodized
30838-128	6 U	8 HP	5	Нет	Screw-on Front	Anodized
30838-148	6 U	28 HP	5	Нет	Screw-on Front	Anodized
30847-556	9 U	84 HP	5	Нет	Screw-on Front	Anodized
30847-484	9 U	12 HP	5		Screw-on Front	Anodized
30847-482	9 U	10 HP	5		Screw-on Front	Anodized
30847-480	9 U	8 HP	5		Screw-on Front	Anodized
30838-126	6 U	6 HP	5	Нет	Screw-on Front	Anodized
30838-127	6 U	7 HP	5	Нет	Screw-on Front	Anodized

Table 2/3

Catalog Number	Rear Finish	Treated Edges	Complies With	EMC Shielding	Высота мм	Material
30847-469	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	217.4 mm	Алюминий
30847-467	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	217.4 mm	Алюминий
30847-460	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	84 mm	Алюминий
30847-461	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	84 mm	Алюминий
30838-162	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий
30847-459	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	84 mm	Алюминий

CatalogNumber	Rear Finish	Treated Edges	Complies With	EMC Shielding	Высота мм	Material
30847-464	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	172.9 mm	Алюминий
30838-123	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий
30838-183	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий
30838-102	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий
30847-465	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	172.9 mm	Алюминий
30838-204	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий
30838-081	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий
30847-468	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	217.4 mm	Алюминий
30847-463	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	172.9 mm	Алюминий
30847-458	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	84 mm	Алюминий
30847-470	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий
30838-053	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий
30838-067	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий
30838-051	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий
30838-045	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий

CatalogNumber	Rear Finish	Treated Edges	Complies With	EMC Shielding	Высота мм	Material
30838-046	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий
30847-471	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий
30838-044	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий
30838-055	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий
30838-043	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий
30838-049	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий
30838-060	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий
30838-047	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий
30847-476	Conductive	Нет		Нет	395.1 mm	Алюминий
30847-462	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	172.9 mm	Алюминий
30838-124	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий
30847-466	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	217.4 mm	Алюминий
30838-125	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий
30838-130	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий
30838-132	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий

CatalogNumber	Rear Finish	Treated Edges	Complies With	EMC Shielding	Высота мм	Material
30838-141	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий
30838-134	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий
30838-136	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий
30838-128	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий
30838-148	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий
30847-556	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	395.1 mm	Алюминий
30847-484	Conductive	Нет		Нет	395.1 mm	Алюминий
30847-482	Conductive	Нет		Нет	395.1 mm	Алюминий
30847-480	Conductive	Нет		Нет	395.1 mm	Алюминий
30838-126	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий
30838-127	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий

Table 3/3				
Catalog Number	Product Type	Type	Ширина мм	Certifications
30847-469	Передняя панель	Front Panel without Handle	426.4 mm	
30847-467	Передняя панель	Front Panel without Handle	213 mm	
30847-460	Передняя панель	Front Panel without Handle	319.7 mm	
30847-461	Передняя панель	Front Panel without Handle	426.4 mm	RoHS

Catalog Number	Product Type	Type	Ширина мм	Certifications
30838-162	Передняя панель	Front Panel without Handle	213 mm	RoHS
30847-459	Передняя панель	Front Panel without Handle	213 mm	
30847-464	Передняя панель	Front Panel without Handle	319.7 mm	RoHS
30838-123	Передняя панель	Front Panel without Handle	426.4 mm	RoHS
30838-183	Передняя панель	Front Panel without Handle	319.7 mm	RoHS
30838-102	Передняя панель	Front Panel without Handle	319.7 mm	RoHS
30847-465	Передняя панель	Front Panel without Handle	426.4 mm	RoHS
30838-204	Передняя панель	Front Panel without Handle	426.4 mm	RoHS
30838-081	Передняя панель	Front Panel without Handle	213 mm	RoHS
30847-468	Передняя панель	Front Panel without Handle	319.7 mm	
30847-463	Передняя панель	Front Panel without Handle	213 mm	RoHS
30847-458	Передняя панель	Front Panel without Handle	141.9 mm	
30847-470	Передняя панель	Front Panel without Handle	9.8 mm	RoHS
30838-053	Передняя панель	Front Panel without Handle	70.8 mm	RoHS
30838-067	Передняя панель	Front Panel without Handle	141.9 mm	RoHS
30838-051	Передняя панель	Front Panel without Handle	60.6 mm	RoHS
30838-045	Передняя панель	Front Panel without Handle	30.1 mm	RoHS
30838-046	Передняя панель	Front Panel without Handle	35.2 mm	RoHS

Catalog Number	Product Type	Type	Ширина мм	Certifications
30847-471	Передняя панель	Front Panel without Handle	14.9 mm	RoHS
30838-044	Передняя панель	Front Panel without Handle	25 mm	RoHS
30838-055	Передняя панель	Front Panel without Handle	80.9 mm	RoHS
30838-043	Передняя панель	Front Panel without Handle	20 mm	RoHS
30838-049	Передняя панель	Front Panel without Handle	50.5 mm	RoHS
30838-060	Передняя панель	Front Panel without Handle	106.3 mm	RoHS
30838-047	Передняя панель	Front Panel without Handle	40.3 mm	RoHS
30847-476	Передняя панель	Front Panel without Handle	20 mm	RoHS
30847-462	Передняя панель	Front Panel without Handle	141.9 mm	
30838-124	Передняя панель	Front Panel without Handle	20 mm	RoHS
30847-466	Передняя панель	Front Panel without Handle	141.9 mm	
30838-125	Передняя панель	Front Panel without Handle	25 mm	RoHS
30838-130	Передняя панель	Front Panel without Handle	50.5 mm	RoHS
30838-132	Передняя панель	Front Panel without Handle	60.6 mm	RoHS
30838-141	Передняя панель	Front Panel without Handle	106.3 mm	RoHS
30838-134	Передняя панель	Front Panel without Handle	70.8 mm	RoHS
30838-136	Передняя панель	Front Panel without Handle	80.9 mm	RoHS
30838-128	Передняя панель	Front Panel without Handle	40.3 mm	RoHS

Catalog Number	Product Type	Type	Ширина мм	Certifications
30838-148	Передняя панель	Front Panel without Handle	141.9 mm	RoHS
30847-556	Передняя панель	Front Panel without Handle	426.4 mm	RoHS
30847-484	Передняя панель	Front Panel without Handle	60.6 mm	RoHS
30847-482	Передняя панель	Front Panel without Handle	50.5 mm	RoHS
30847-480	Передняя панель	Front Panel without Handle	40.3 mm	RoHS
30838-126	Передняя панель	Front Panel without Handle	30.1 mm	RoHS
30838-127	Передняя панель	Front Panel without Handle	35.2 mm	RoHS

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE