


# Outdoor Unibody HEX

## Power Utilities



Telecom and Railway applications require sophisticated electronics in outdoor setups. nVent SCHROFF Outdoor cabinets shield such electronic components from extreme weather and vandalism, ensuring operational continuity.

### CERTIFICATIONS



### FEATURES

Double-walled, Al

Forced heat dissipation via integrated heat exchanger in the door, max. 70 W/K

IP 55

One-piece inner case with removable outer cladding

### SPECIFICATIONS

Table 1/2

Catalog Number	Product Type	Product Family	Rack Height	Height	Width	Depth
11249-016	Outdoor Cabinet	Unibody	25 U	1330 mm	700 mm	500 mm

Table 2/2

Catalog Number	Wall Type	Door Type	Access	Cooling	EMC Shielding	Complies With
11249-016	Double Walled	Single Door	Front	Air-to-Air Heat Exchanger	No	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**