

Varistar CP Bottom Rear Panel, Shortened

Power Utilities

Shortened Rear Panel available for IP20, IP55 and EMC applications.

Shortened rear panels ensure efficient cable management.

FEATURES

Screw fixed, Robust and Single person mountable Side Panel

Plain or with brush strip

Height of connection plate 400 mm

SPECIFICATIONS

Table 1/2

Catalog Number	Rack Height	Высота мм	Ширина мм	Protection Rating	Color	Color Code
21630-354	38 U	1800 mm	600 mm	IP55	Black Grey	RAL 7021
21630-355	38 U	1800 mm	800 mm	IP55	Black Grey	RAL 7021
21630-356	42 U	2000 mm	600 mm	IP55	Black Grey	RAL 7021
21630-357	42 U	2000 mm	800 mm	IP55	Black Grey	RAL 7021
21630-358	47 U	2200 mm	600 mm	IP55	Black Grey	RAL 7021
21630-359	47 U	2200 mm	800 mm	IP55	Black Grey	RAL 7021

Table 2/2

Catalog Number	Product Type
21630-354	Cabinet Door

Catalog Number	Product Type
21630-355	Cabinet Door
21630-356	Cabinet Door
21630-357	Cabinet Door
21630-358	Cabinet Door
21630-359	Cabinet Door

ADDITIONAL PRODUCT DETAILS

The height of the rear panel is 400 mm less than the cabinet height to accomodate the connecting plate.

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE