

Varistar CP Deco Cabinet With 19" Panel Mounts in Deco Frame

Power Utilities

Varistar: Highly versatile, robust welded steel frame electronics cabinet with a wide range of available features including protection against dust and water (IP 20 and IP 55), cooling options from fans to 40kW air-to-water chillers, shock, vibration and seismic resistance up to NEBS GR-63-CORE Bellcore zone 4 and industry leading radio-frequency/electromagnetic (RFI / EMI) shielding of 60 dB at 1 GHz, 40 dB at 3 GHz (tested to IEC 61587-3).

FEATURES

Open at front (no door)

19" panel mounts integrated into decoration frame

Rear door with single point locking, side panels with quick release fastener

Static load-carrying capacity 400 kg (mounted at decoration frame)

SPECIFICATIONS

Table 1/3

Catalog Number	Rack Height	Высота мм	Frame Color	Ширина мм	Frame Color Code	Cladding Material
10630-034	38 U	1800 mm	Black Grey	600 mm	RAL 7021	Сталь
10630-033	38 U	1800 mm	Black Grey	600 mm	RAL 7021	Сталь
10630-035	42 U	2000 mm	Black Grey	600 mm	RAL 7021	Сталь
10630-036	42 U	2000 mm	Black Grey	600 mm	RAL 7021	Сталь

Table 2/3

Catalog Number	Глубина мм	Cladding Color	Cladding Color Code	Complies With	Frame Material	Product Type
----------------	------------	----------------	---------------------	---------------	----------------	--------------

10630-034	800 mm	Black Grey	RAL 7021	IEC 60297-3-100	Сталь	Cabinet
10630-033	600 mm	Black Grey	RAL 7021	IEC 60297-3-100	Сталь	Cabinet
10630-035	600 mm	Black Grey	RAL 7021	IEC 60297-3-100	Сталь	Cabinet
10630-036	800 mm	Black Grey	RAL 7021	IEC 60297-3-100	Сталь	Cabinet

Table 3/3

Catalog Number	Static Load
10630-034	400 kgf
10630-033	400 kgf
10630-035	400 kgf
10630-036	400 kgf

ADDITIONAL PRODUCT DETAILS

Lever handle can be added to rear door.

Further dimensions and version available on ServicePlus EMC. Please order base/plinth separately. For assembly of shelves and slide rails another pair of panel/slide mounts is necessary.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE