

Varistar CP Plain Steel Door, Seismic EMC and IP55, Multi-Point Locking

Power Utilities

EMC and IP55 Steel Door with lever handle and 4-Point locking.

FEATURES

Lever handle with push button

Opening angle 180°

Steel door with Multi-Point locking for Seismic & EMC applications

SPECIFICATIONS

Table 1/2

Catalog Number	Rack Height	Высота мм	Ширина мм	Color	Color Code	Complies With
21630-760	33 U	1600 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529
21630-761	33 U	1600 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529
21630-762	38 U	1800 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529
21630-763	38 U	1800 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529
21630-764	42 U	2000 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529

CatalogNumber	Rack Height	Высота мм	Ширина мм	Color	Color Code	Complies With
21630-765	42 U	2000 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529
21630-766	47 U	2200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529
21630-767	47 U	2200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529

Table 2/2						
Catalog Number	Locking Type	Material	Product Type	Protection Rating	Type	Works With
21630-760	4-Point Locking	Сталь	Cabinet Door	IP55	Сплошная стальная дверь	Varistar CP
21630-761	4-Point Locking	Сталь	Cabinet Door	IP55	Сплошная стальная дверь	Varistar CP
21630-762	4-Point Locking	Сталь	Cabinet Door	IP55	Сплошная стальная дверь	Varistar CP
21630-763	4-Point Locking	Сталь	Cabinet Door	IP55	Сплошная стальная дверь	Varistar CP
21630-764	4-Point Locking	Сталь	Cabinet Door	IP55	Сплошная стальная дверь	Varistar CP
21630-765	4-Point Locking	Сталь	Cabinet Door	IP55	Сплошная стальная дверь	Varistar CP
21630-766	5-Point Locking	Сталь	Cabinet Door	IP55	Сплошная стальная дверь	Varistar CP
21630-767	5-Point Locking	Сталь	Cabinet Door	IP55	Сплошная стальная дверь	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE