

19-дюймовый выдвижной ящик



19-дюймовые выдвижные ящики позволяют устанавливать портативные компьютеры, рабочие поверхности для удобства эксплуатации. 19-дюймовый выдвижной ящик SCHROFF имеет грузоподъемность 15 КГ, что позволяет установить в него целый ряд компонентов.

CERTIFICATIONS



FEATURES

Допустимая статическая нагрузка 15 кг

Возможна дополнительная комплектация столешницей

Возможна дополнительная комплектация столешницей

Допустимая статическая нагрузка 15 кг

SPECIFICATIONS

Static Load: 15kg
Product Type: Cabinet/Rack Drawer
Material: Сталь

Table 1/2

Catalog Number	Rack Height	Finish	Package Quantity	Color	Color Code	Front Finish
20110-054	1U	Powder Coated	1	Light Grey	RAL 7035	
20110-061	1U	Powder Coated	1			Anodized

CatalogNumber	Rack Height	Finish	Package Quantity	Color	Color Code	Front Finish
20110-180	1U	Powder Coated	1	Black Grey	RAL 7021	
20110-055	2U	Powder Coated	1	Light Grey	RAL 7035	
20110-056	3U	Powder Coated	1	Light Grey	RAL 7035	
20110-062	2U	Powder Coated	1			Anodized
20110-063	3U	Powder Coated	1			Anodized
20110-181	2U	Powder Coated	1	Black Grey	RAL 7021	
20110-182	3U	Powder Coated	1	Black Grey	RAL 7021	

Table 2/2

Catalog Number	Type	Works With	Quick Ship
20110-054	Выдвижной ящик	19" Cabinets	No
20110-061	Выдвижной ящик	19" Cabinets	No
20110-180	Выдвижной ящик	19" Cabinets	No
20110-055	Выдвижной ящик	19" Cabinets	No
20110-056	Выдвижной ящик	19" Cabinets	No
20110-062	Выдвижной ящик	19" Cabinets	No
20110-063	Выдвижной ящик	19" Cabinets	No
20110-181	Выдвижной ящик	19" Cabinets	No
20110-182	Выдвижной ящик	19" Cabinets	No

ADDITIONAL PRODUCT DETAILS

Монтажный комплект для сборки на 19 дюймов заказывается отдельно.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE