

19-дюймовый вентиляторный блок, 1 U, Контроль и мониторинг частоты вращения

Вентиляторный блок для установки в пространство 1 U
внутри шкафа.



CERTIFICATIONS



FEATURES

Настраиваемый диапазон: 20 ... 40 °C и 30 ... 50 °C

Сниженные шумовые характеристики за счет регулировки воздушного потока в зависимости от температуры

Внешний датчик, в случае отказа, по умолчанию - переход на максимальную скорость вращения

Система контроля со светодиодными индикаторами и беспотенциальным контактом

Защита от прикосновения в соответствии с DIN EN ISO 13857

SPECIFICATIONS

Table 1/2

Catalog Number	Input Voltage AC	Input Voltage DC	Package Quantity	Finish	Material	Certifications
10713-098		24V min	1	Aluminum-Zinc Plated, Anodized	Сталь, Алюминий	CE, RoHS, EAC
19713-121	230V		1	Aluminum-Zinc Plated, Anodized	Сталь, Алюминий	EAC, RoHS

CatalogNumber	Input Voltage AC	Input Voltage DC	Package Quantity	Finish	Material	Certifications
19713-006	230V		1	Aluminum-Zinc Plated, Anodized	Сталь, Алюминий	CE, RoHS, EAC
10713-099		24V min	1	Aluminum-Zinc Plated, Anodized	Сталь, Алюминий	EAC, CE, RoHS

Table 2/2

Catalog Number	Quick Ship
10713-098	No
19713-121	No
19713-006	No
10713-099	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE