

19-дюймовый распределитель питания, 3-фазный



19-дюймовый распределительный блок с 3-фазным входом и автоматическими выключателями. Блок предоставляет розетки IEC C19 для оборудования или однофазных источников питания.

CERTIFICATIONS



FEATURES

3-фазный распределитель питания для подключения однофазных потребителей или блоков розеток

Вход 3-фазный 400 В перем. тока

Выход через розетки IEC 60320-C19

Защита от перегрузки по току для каждого выхода

SPECIFICATIONS

Глубина мм: 250mm

Product Type: Power Distributor

Table 1/1

Catalog Number	Package Quantity	Finish	Высота мм	Длина мм	Material	Quick Ship
60110-365	1	Anodized	131mm	484mm	Алюминий, Polyamide	No

CatalogNumber	Package Quantity	Finish	Высота мм	Длина мм	Material	Quick Ship
60110-366	1	Anodized	131mm	484mm	Алюминий, Polyamide	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE