

AC Fan

Осевой вентилятор, 119 мм, с входом переменного тока.
Запасная деталь для лотков вентиляторов 1 U.



CERTIFICATIONS



FEATURES

Вентилятор 119 мм постоянного тока со штекером для соединительного кабеля

SPECIFICATIONS

Table 1/3

Catalog Number	Works With	Ширина мм	Длина мм	Высота мм	Voltage AC	Частота
20713-243	19" Fan Trays	119mm	119mm	38mm	230V	50/60 Hz
20713-244	19" Fan Trays	119mm	119mm	38mm	115V	50/60 Hz
20700-001	19" Fan Trays	119mm	119mm	25mm	230V	50/60 Hz
20713-147	19" Fan Trays	119mm	119mm	25mm	115V	50/60 Hz
20713-142	19" Fan Trays	119mm	119mm	25mm	230V	50/60 Hz

CatalogNumber	Works With	Ширина мм	Длина мм	Высота мм	Voltage AC	Частота
20713-146	19" Fan Trays	119mm	119mm	25mm	115V	50/60 Hz

Table 2/3

Catalog Number	Airflow @ 50 Hz	Airflow @ 60 Hz	Noise Level @ 50 Hz	Noise Level @ 60 Hz	Power @ 50 Hz	Power @ 60 Hz
20713-243	162m³/h	192m³/h	37dB(A)	41dB(A)	15W	14W
20713-244	162m³/h	192m³/h	37dB(A)	41dB(A)	15W	14W
20700-001	108m³/h	120m³/h	34dB(A)	38dB(A)	14W	11W
20713-147	108m³/h	120m³/h	34dB(A)	38dB(A)	14W	11W
20713-142	84m³/h	90m³/h	29dB(A)	30dB(A)	8W	7W
20713-146	84m³/h	90m³/h	29dB(A)	30dB(A)	8W	7W

Table 3/3

Catalog Number	Max Static Pressure	Ambient Temperature	Package Quantity	Quick Ship
20713-243	73Pa	70°C	1	No
20713-244	73Pa	70°C	1	No
20700-001	41Pa	70°C	1	No
20713-147	41Pa	70°C	1	No
20713-142	23Pa	70°C	1	No
20713-146	23Pa	70°C	1	No

ADDITIONAL PRODUCT DETAILS

Соединительный кабель и защитная решетка заказываются отдельно.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE