

Бортовой каркас



Подходит для применения в условиях постоянных вибраций, ударов, высоких температур и высокой влажности.

CERTIFICATIONS



FEATURES

Для передвижного железнодорожного оборудования

Подходит для использования в условиях постоянных вибраций, ударной нагрузки, высоких температур, и высокой влажности

Подходит для блочных каркасов высотой 1, 2, or 3 U SNCF sub racks (NF F61-005, CF 60-002)

Задняя сторона предназначена для стандартных разъемов; траверса может быть сконфигурирована для кодовых штифтов SNCF

Траверса со встроенным кабельным каналом

Несколько стоек можно штабелировать или смонтировать в ряд

Произведена с использованием сварочного процесса, certified to EN 15085 (CL2)

Stainless Steel welds passivated to prevent corrosion

SPECIFICATIONS

Static Load:	25kg
Глубина мм:	341.8mm
Product Type:	Rack
Complies With:	SNCF NFF 61005; SNCF NFF 60002
Frame Material:	Сталь

Table 1/2

Catalog Number	Rack Height	Высота мм	Rack Width	Ширина мм	Package Quantity	Material
10170-013	6U	290mm	36HP	252.65mm	1	Нержавеющая сталь
10170-017	9U	423.4mm	36HP	252.65mm	1	Нержавеющая сталь
10170-012	6U	290mm	84HP	496.4mm	1	Нержавеющая сталь
10170-016	9U	423.4mm	84HP	496.4mm	1	Нержавеющая сталь
10170-014	3U	156.7mm	84HP	496.4mm	1	Нержавеющая сталь
10170-015	3U	156.7mm	36HP	252.65mm	1	Нержавеющая сталь

Table 2/2

Catalog Number	Quick Ship
10170-013	No
10170-017	No
10170-012	No
10170-016	No
10170-014	No
10170-015	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE