


19-дюймовый блок питания Coolpower с преобразованием постоянного напряжения в постоянное, мощность 100 Вт, с одним выходом, CPDC212

CATALOG NUMBER

13103-007



Pluggable 19" Power Supplies with H15 connector for fanless applications.

CERTIFICATIONS



FEATURES

Широкий диапазон входного напряжения от 20 до 72 В пост. тока,

Гальваническая изоляция между первичной и вторичной цепями

Высокая удельная мощность

PRODUCT ATTRIBUTES

Product Type: Power Supply

Type: 19" DC/DC Converter

Input Voltage DC: 20 – 72V

Мощность W: 108W

Number of Output Voltages: 1

Voltage 1: 24V

Current 1: 4.5A

Rack Height: 3U

Rack Width: 6HP

Глубина мм: 171.93mm

Package Quantity: 1

ADDITIONAL PRODUCT DETAILS

Для входного напряжения 100 - 360 В пост. тока см. импульсный источник питания перем. / пост. тока.

Передняя панель заказывается отдельно.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE