



19-дюймовый выдвижной ящик, высота 3 U, RAL 7035

CATALOG NUMBER

20110-056



19-дюймовые выдвижные ящики позволяют устанавливать портативные компьютеры, рабочие поверхности для удобства эксплуатации. 19-дюймовый выдвижной ящик SCHROFF имеет грузоподъемность 15 КГ, что позволяет установить в него целый ряд компонентов.

CERTIFICATIONS



FEATURES

Допустимая статическая нагрузка 15 кг

Возможна дополнительная комплектация столешницей

Возможна дополнительная комплектация столешницей

Допустимая статическая нагрузка 15 кг

PRODUCT ATTRIBUTES

Rack Height: 3U
Finish: Powder Coated
Package Quantity: 1
Color: Light Grey
Color Code: RAL 7035
Type: Выдвижной ящик
Material: Сталь
Product Type: Cabinet/Rack Drawer
Static Load: 15kg
Works With: 19" Cabinets
Net Weight: 10.03kg

ADDITIONAL PRODUCT DETAILS

Монтажный комплект для сборки на 19 дюймов заказывается отдельно.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE