


19-дюймовая опора под оборудование Labrack, высота 2 U

CATALOG NUMBER

20119-257



Кронштейн для 19-дюймового оборудования, 2 U тип C с макс. нагрузкой 25 кг.

CERTIFICATIONS



FEATURES

Допустимая статическая нагрузка 25 кг

Монтажная высота 2 U

Выступ спереди мин. 168 мм

PRODUCT ATTRIBUTES

Product Type: Полка с креплением на каркасе

Product Family: Лабораторная стойка

Type: Equipment Shelf

Material: Сталь

Finish: Powder Coated

Rack Height: 2U

Ширина мм: 430mm

Глубина мм: 400mm

Net Weight: 3.13kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY**ERICO****HOFFMAN****ILSCO****SCHROFF****TRACHTE**