

Система VPX, повышенной прочности, 10 U, 10 слотов, подключаемый источник питания

CATALOG NUMBER

20836-780



Усиленная система VPX для 10 печатных плат VPX 6 U, 1-дюймовых, 160-миллиметровых и 10 задних плат ввода/вывода. Питание системы осуществляется от сменного источника питания VPX. Модуль управления вентилятором контролирует работу вентиляторов, следит за температурой и напряжением.

FEATURES

Система разработана в соответствии с: MIL-STD-810F, MIL-STD-167, MIL-STD-461, IP 20

Для эксплуатации в сложных условиях с повышенной устойчивостью к ударным нагрузкам и вибрации

Блоки питания, 1 сменный источник питания, 1000 Вт, 6 U, место для второго источника питания

Входное напряжение с задней стороны 100 до 240 В пер. тока, главный выключатель на передней панели шасси

Светодиодный индикатор напряжения и отказа вентилятора на передней панели

6 U каркас для плат спереди и 6U каркас для плат сзади для Rear I/O, с объединительной платой VPX на 10 слотов

Подготовка под телескопические направляющие

Оптимальная защита от электромагнитных помех посредством передней и задней панели со встроенным фильтром Honeycomp

Backplane VPX 10 slot, 6 U, in accordance with VITA 65, Backplane Profile BKP6-CEN10-11.2.4.4

PRODUCT ATTRIBUTES

Product Type: System

Number of Slots: 10

Type: Rugged 19" Rack Mount

Backplane Type: VPX, VITA 65

Data Transfer: 10 GbE; PCIe Gen3

Power per Slot: 50W

Input Voltage AC: 100 – 240V

Airflow Direction: Front to Rear

Rack Height: 10U

Power Supply Type: (1) Pluggable PSU

Power Supply Included: Да

Rear I/O: Да

Complies With: ANSI/VITA 46.0-2019

Мощность W: 1000W

Глубина мм: 490mm

Высота мм: 443.7mm

Ширина мм: 480mm

Package Quantity: 1

ADDITIONAL PRODUCT DETAILS

Модифицированные системы доступны по запросу.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:

nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE