


Передняя панель источника питания для PSK, с тремя выходами

CATALOG NUMBER

21005-470



Передняя панель для источника питания, совместимого с 19-дюймовым решением nVent SCHROFF. Плоская передняя панель с вертикальными канавками для контактных лент ЭМС из нержавеющей стали.

CERTIFICATIONS



FEATURES

передняя панель, алюминий, лицевая поверхность анодированная, тыльная поверхность электропроводящая, С вертикальными слотами для контактных лент ЭМС

PRODUCT ATTRIBUTES

Product Type: Передняя панель

Аксессуар Тип: Передняя панель

Material: Алюминий

Front Finish: Anodized

Rear Finish: Conductive

Treated Edges: Het

Rack Height: 3U

Высота мм: 128.4mm

Rack Width: 6HP

Ширина мм: 30.14mm

Глубина мм: 2.5mm

Package Quantity: 1

Finish: Anodized

Net Weight: 0.054kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE