


Металлическая втулка M2.5, латунь, никелированная, 100 шт.

CATALOG NUMBER

21100-886



Втулка служит направляющей для винта с проточкой при креплении передней панели.

CERTIFICATIONS



FEATURES

Втулка служит направляющей для винта с проточкой при креплении передней панели

Втулка вставляется в удлиненное отверстие в передней панели

PRODUCT ATTRIBUTES

Material: Brass

Finish: Organic Top Coat

Package Quantity: 100

Глубина мм (D): 4.4mm

Высота мм (H): 6mm

Product Type: Sleeve


Ширина мм (W): 8mm

ADDITIONAL PRODUCT DETAILS

Металлические втулки на передних панелях неполной ширины должны запрессованы.

Все втулки можно использовать для передних панелей с шириной стойки больше 2 HP (Horizontal Pitch).

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE