


Комплект для ЭМС-экранирования из нержавеющей стали для передней панели, высота 6 U, 100 шт.

CATALOG NUMBER

21101-708



ЭМС-прокладки из нержавеющей стали вставляются в боковые слоты экранируемых передних панелей (по 2 штуки на каждую переднюю панель).

CERTIFICATIONS



FEATURES

ЭМС-прокладки из нержавеющей стали вставляются в боковые слоты экранируемых передних панелей (по 2 штуки на каждую переднюю панель)

ЭМС-накладка, нержавеющая сталь

Temperature range -200 °C ... +160 °C

PRODUCT ATTRIBUTES

Rack Height: 6U

Package Quantity: 100

Material: Нержавеющая сталь

Product Family: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; PropacPRO; Frame Type Plug-In Unit


Product Type: Shielding Kit

Works With: Блочный каркас; Coffrets; Передние панели

ADDITIONAL PRODUCT DETAILS

Монтажный инструмент заказывается отдельно.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE