


Приподнятая верхняя крышка Euro rack, RAL 7021, ширина 600, глубина 900

CATALOG NUMBER

22117-813



Приподнятая крышка для лучшей вентиляции и выхода тепла. Рельефная верхняя крышка Euro rack прочная, лоток вентилятора может быть модернизирован для вентиляции.

CERTIFICATIONS



FEATURES

Верхняя крышка, сталь, 1,5 мм

Воздушный просвет 8 мм

Лоток вентилятора может быть модернизирован для вентиляции

PRODUCT ATTRIBUTES

Ширина мм: 600mm

Глубина мм: 900mm

Package Quantity: 1

Color: Black Grey

Color Code: RAL 7021

Finish: Powder Coated

Material: Сталь

Product Family: Eurorack

Product Type: Cabinet/Rack Top Cover

Protection Rating: IP20

Type: Raised

Gross Weight: 8.08kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE