


Винт со сферо-цилиндрической головкой, под отвертку Torx, с функцией заземления, стальной оцинкованный, М4 × 14 мм, 100 шт.

CATALOG NUMBER

24560-130



Accessory parts like screws, washer and nuts enable the mounting of subrack components.

CERTIFICATIONS



FEATURES

For fixing of subrack components

PRODUCT ATTRIBUTES

Длина мм: 14mm

Package Quantity: 100

Thread Size: M4

Finish: Zinc Plated

Material: Сталь

Product Family: EuropacPRO

Product Type: Screw

Type: Panhead Screw

Works With: Блочный каркас

Net Weight: 0.22kg

Torque: 2.4N·m

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE