


Винт со сферо-цилиндрической головкой, Torx, диаметр 2,5 мм, длина 9,3 мм, саморез, стальной оцинкованный

CATALOG NUMBER

24560-141



Винты с потайной головкой.

CERTIFICATIONS



FEATURES

Винт с потайной головкой с Torx, самоформирующийся

Для монтажа трапециевидных ручек на передней панели сменных блоков PRO каркасного типа

PRODUCT ATTRIBUTES

Длина мм: 9.3mm

Package Quantity: 100

Thread Size: M2.5

Finish: Zinc Plated

Material: Сталь

Product Family: Frame Type Plug-In Unit

Product Type: Screw

Type: Panhead Screw

Works With: Направляющие для плат

Gross Weight: 0.04kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff

Middle East & India

Dubai, United Arab **Emirates** +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE