

Изоляционная полоска горизонтального рельса, 84 HP, поликарбонат

CATALOG NUMBER

24560-884



Планка обеспечивает изолированный монтаж объединительных плат или металлических панелей в качестве опор для разъемов. Создает стандартизированную монтажную глубину для вставных блоков в блочном каркасе в сочетании с горизонтальными рельсами L-ST и H-ST. Подходит для RatiopacPRO/-AIR, Propac Pro, CompacPRO и EuropacPRO/-Rugged.

CERTIFICATIONS



FEATURES

Для изолированного монтажа объединительных плат или металлических панелей в качестве опор для разъемов

Создает стандартизированную монтажную глубину для вставных блоков в блочном каркасе в сочетании с горизонтальными рельсами L-ST и H-ST

PRODUCT ATTRIBUTES

Rack Width: 84HP

Package Quantity: 10

Flammability Rating: UL® 94V-0

Длина мм: 428.64mm

Material: Polycarbonate

Product Family: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; Inpac

Product Type: Insulation Strip

Works With: Блочный каркас; Coffrets

ADDITIONAL PRODUCT DETAILS

Обратите внимание, что поставки доступны в указанных стандартных товарных партиях (товарная партия, например, 5 шт., 10 шт., 50 шт. и т. д.). Другие объемы заказов (например, 2 шт.) могут округляться вверх до следующего возможного размера стандартной товарной партии.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE