

# Универсальный теплопроводник (FHC) Interscale, 20 мм

## CATALOG NUMBER

**24830-005**



Расширение и сжатие теплопроводного блока по вертикали компенсирует наложение допусков и обеспечивает оптимальный поверхностный контакт и давление вдоль канала теплоотвода, что позволяет обойтись без теплопроводящей подложки.

## CERTIFICATIONS



## FEATURES

Поддержка процессоров Intel,, AMD, Via,, Freescale,, Поддержка процессоров NVidia и Texas Instrument для цоколей BGA

Непревзойденная эффективность кондуктивного охлаждения, Повышение эффективности на 10% по сравнению с традиционными методами кондуктивного охлаждения

Система кондуктивного охлаждения для компактного электронного оборудования Small Form Factor (подана заявка на патент)

Крепление к печатной плате с помощью теплопроводной клейкой ленты

Расширение и сжатие теплопроводного блока по вертикали компенсирует наложение допусков и обеспечивает оптимальный поверхностный контакт и давление вдоль канала теплоотвода, что позволяет обойтись без теплопроводящей подложки

Подходит для корпусов Interscale C

## PRODUCT ATTRIBUTES

Product Type: Conductor Block

Product Family: Interscale

Type: Heat Conductor

Works With: Coffrets

Package Quantity: 1

Глубина мм: 22mm

Ширина мм: 22mm

Finish: Anodized; Aluminum-Zinc Plated

Gross Weight: 0.074kg

Material: Алюминий; Сталь

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**