



Горизонтальная рейка, передняя, тип H-LD, усиленная, длинная кромка, для применения согласно IEEE, 63 HP

CATALOG NUMBER

34560-363



Combinations of horizontal rails and side panels

“+” = can be combined, “-” = combination not recommended

	Horizontal rail	Horizontal rail with side panel	Horizontal rail with side panel (for connection)	Horizontal rail with side panel (for connection)
Horizontal rail	-	+	+	+
Horizontal rail with side panel	+	+	+	+
Horizontal rail with side panel (for connection)	+	+	-	-
Horizontal rail with side panel (for connection)	+	+	-	-

Horizontal rail with side panel (for connection)

Горизонтальная рейка с длинной кромкой позволяет использовать ручки для вставки/извлечения согласно IEEE.

CERTIFICATIONS



FEATURES

Для вставных модулей с ручкой IEEE

Длинная кромка (H-LD)

Монтаж в верхнем и нижнем положении

Для систем CPCI и VME64x

Алюминиевый экструдированный профиль, анодированная поверхность, электропроводящая контактная поверхность

PRODUCT ATTRIBUTES

Rack Width: 63HP

Package Quantity: 1

Finish: Anodized

Длина мм: 325.12mm

Material: Алюминий

Product Family: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO

Product Type: Горизонтальный рельс

Type: Heavy, LD

Works With: Блочный каркас; Coffrets

Gross Weight: 0.128kg

ADDITIONAL PRODUCT DETAILS

Поставка исключительно в размере товарной партии. Цена указана за отдельную единицу.

Обратите внимание, что поставки доступны в указанных стандартных товарных партиях (товарная партия, например, 5 шт., 10 шт., 50 шт. и т. д.). Другие объемы заказов (например, 2 шт.) могут округляться вверх до следующего возможного размера стандартной товарной партии.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE