


Сетевой кабель, США к IEC C13

CATALOG NUMBER

60103-141



Сетевой кабель nVent SCHROFF обеспечивает практичное, универсальное крепление с помощью различных крепежных приспособлений. Он является универсальным по своей сущности и подходит для различных типов применения, таких как вентиляторы, освещение шкафов и т. д., соединения промышленных ПК, источники бесперебойного питания, системы.

CERTIFICATIONS



FEATURES

Области применения: вентиляторы, освещение шкафа, подключение к промышленному ПК, системы и источники бесперебойного питания

PRODUCT ATTRIBUTES

Input Connector: US = US Standard

Output Connector: IEC C13

Длина мм: 2500mm

Package Quantity: 1

Color: Черный

Connector Type: Straight

Material: PVC

Product Type: Cable

Net Weight: 0.165kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE