

EuropacPRO 19" Subrack Kit for DIN Connector, возможно дооснащение экранированием

Неэкранированный блочный каркас для монтажа Din-разъема 60603-2 (DIN 41612).



CERTIFICATIONS



FEATURES

Блочный каркас с боковой стенкой типа F («гибкий»), передний 19-дюймовый кронштейн входит в комплект поставки, 19-дюймовый кронштейн с регулируемой глубиной заказывается отдельно

Алюминиевая конструкция

IP 20 в соответствии с IEC 60529

Внутренние и внешние размеры соответствуют IEC 60297-3-100, -101, IEEE 1101.1

Задние горизонтальные рейки для монтажа разъема (IEC 60603-2/DIN 41612)

Доступны модификации, включающие вырезы, различные варианты отделки или размеры

Поставляется в компактной плоской упаковке

Горизонтальная рейка типа «light»

SPECIFICATIONS

Material:	Алюминий
Finish:	Anodized; Passivated
EMC Shielding:	Нет
Product Type:	Subrack/Chassis

Table 1/2

Catalog Number	Rack Height	Глубина мм	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24563-191	3U	175mm	1	DIN Connector	160mm	Stainless Steel (retrofittable)
24563-192	3U	235mm	1	DIN Connector	160mm, 220mm	Stainless Steel (retrofittable)
24563-193	3U	295mm	1	DIN Connector	160mm, 220mm, 280mm	Stainless Steel (retrofittable)
24563-194	3U	355mm	1	DIN Connector	160mm, 220mm, 280mm, 340mm	Stainless Steel (retrofittable)
24563-491	6U	175mm	1	DIN Connector	160mm	Stainless Steel (retrofittable)
24563-492	6U	235mm	1	DIN Connector	160mm, 220mm	Stainless Steel (retrofittable)
24563-493	6U	295mm	1	DIN Connector	160mm, 220mm, 280mm	Stainless Steel (retrofittable)
24563-494	6U	355mm	1	DIN Connector	160mm, 220mm, 280mm, 340mm	Stainless Steel (retrofittable)

Table 2/2

Catalog Number	Handle Included	Mounting	Complies With	Rack Width	Static Load	Quick Ship
24563-191	Нет	Rack	IEC 60297-3-103	84HP	11kg	No
24563-192	Нет	Rack	IEC 60297-3-103	84HP	11kg	No
24563-193	Нет	Rack	IEC 60297-3-103	84HP	11kg	No
24563-194	Нет	Rack	IEC 60297-3-103	84HP	11kg	No
24563-491	Нет	Rack	IEC 60297-3-103	84HP	11kg	No
24563-492	Нет	Rack	IEC 60297-3-103	84HP	11kg	No

CatalogNumber	HandleIncluded	Mounting	Complies With	Rack Width	Static Load	Quick Ship
24563-493	Нет	Rack	IEC 60297-3-103	84HP	11kg	No
24563-494	Нет	Rack	IEC 60297-3-103	84HP	11kg	No

ADDITIONAL PRODUCT DETAILS

Индивидуальная конфигурация: широкий выбор вариантов по высоте, ширине и глубине; направляющие для самых разных применений; выбор вариантов внутреннего оснащения, принадлежностей и монтажного материала.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE