

Мезонинная передняя панель РМС, Без экранирования



Мезонинная передняя панель вставляется в вырезы передней панели РМС. Доступна в различных вариантах обработки.

CERTIFICATIONS



FEATURES

Мезонинная передняя панель монтируется в выемки РМС

ЭМС-экранирование с электропроводящим уплотнительным кольцом

SPECIFICATIONS

Table 1/3							
Catalog Number	Туре	Аксессуар Тип	Mounting	EMC Shielding	Gasket Type	Material	
20835-899	Mezzanine Front Panel	Передняя панель	Snapped in	No (Retrofittable)	O-Ring EMC	Алюминий	
20835-896	Front Panel without Handle		Screw-on Front	No (Retrofittable)		Zinc	
20835-931	Front Panel without Handle		Screw-on Front	No (Retrofittable)		Zinc	
20835-929	Front Panel without Handle		Screw-on Front	No (Retrofittable)		Zinc	

Table 2/3							
Catalog Number	Front Finish	Rear Finish	Treated Edges	Высота мм	Ширина мм	Complies With	
20835-899	Anodized	Conductive	Да	74mm	12.7mm	Мезионная PMC, IEEE P1386	
20835-896	Anodized	Anodized	Нет	74mm	12.7mm	Мезионная PMC, IEEE P1386	
20835-931	Anodized	Conductive	Нет	74mm	12.7mm	Мезионная PMC, IEEE P1386	
20835-929	Chrome Plated	Chrome Plated	Да	74mm	12.7mm	Мезионная PMC, IEEE P1386	

Table 3/3							
Catalog Number	Глубина мм	Package Quantity	Finish	Quick Ship			
20835-899	2.5mm	10	Anodized	No			
20835-896		10		No			
20835-931		10		No			
20835-929		10		No			

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE