

19-дюймовый линейный регулятор переменного/постоянного тока для источника питания, Двойной

Линейный регулятор предназначен для приложений, где допускается только очень низкий уровень шума на выходах.



CERTIFICATIONS



FEATURES

2 выходных напряжения, гальваническая развязка

Высокая точность управления, низкий уровень пульсаций и очень низкий уровень помех

Входное напряжение 230 В перем. тока (можно переключить на 115 В перем. тока с набором для преобразования входного напряжения)

Возможно применение в медицинском оборудовании (расстояние между токоведущими печатными проводниками 8 мм)

SPECIFICATIONS

Table 1/3

Catalog Number	Type	Input Voltage AC	Мощность W	Number of Output Voltages	Voltage 1	Current 1
13105-018	19" Linear Regulator	230V	12W	2	15V	0.4A

CatalogNumber	Type	Input Voltage AC	Мощность W	Number of OutputVoltages	Voltage 1	Current 1
13105-017	19" Linear Regulator	230V	10W	2	12V	0.4A
13105-022	19" Linear Regulator	230V	24W	2	12V	1A
13105-023	19" Linear Regulator	230V	30W	2	15V	1A
13105-029	19" Linear Regulator	230V	58W	2	24V	1.2A
13105-028	19" Linear Regulator	230V	45W	2	15V	1.5A
13105-021	19" Linear Regulator	230V	14W	2	5V	1.4A
13105-027	19" Linear Regulator	230V	36W	2	12V	1.5A

Table 2/3						
Catalog Number	Voltage 2	Current 2	Rack Height	Rack Width	Глубина мм	Package Quantity
13105-018	15V	0.4A	3U	6HP	171.93mm	1
13105-017	12V	0.4A	3U	6HP	171.93mm	1
13105-022	12V	1A	3U	10HP	171.93mm	1
13105-023	15V	1A	3U	10HP	171.93mm	1
13105-029	24V	1.2A	3U	14HP	171.93mm	1
13105-028	15V	1.5A	3U	14HP	171.93mm	1
13105-021	5V	1.4A	3U	10HP	171.93mm	1
13105-027	12V	1.5A	3U	14HP	171.93mm	1

Table 3/3		
Catalog Number	Certifications	Quick Ship

13105-018	EN 62368-1, RoHS, CE	No
13105-017	EN 62368-1, RoHS, CE	No
13105-022	CE, RoHS	No
13105-023	CE, RoHS	No
13105-029	CE, RoHS	No
13105-028	RoHS, CE	No
13105-021	RoHS, CE	No
13105-027	RoHS, CE	No

ADDITIONAL PRODUCT DETAILS

Передняя панель заказывается отдельно.

Выходные данные в $T_a = 0 \dots 50^\circ\text{C}$.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE