

19-дюймовый линейный регулятор переменного/постоянного тока для источника питания, одинарный

Линейный регулятор для вариантов применения, где требуется очень низкий уровень выходного шума.



CERTIFICATIONS



FEATURES

1 выходное напряжение

Высокая точность управления, низкая остаточная пульсация и низкий уровень помех

Сетевое/линейное напряжение 230 В перем. тока (можно переключить на 115 В перем. тока с набором для преобразования сетевого/линейного напряжения)

Возможно применение в медицинском оборудовании (расстояние между токоведущими печатными проводниками 8 мм)

SPECIFICATIONS

Table 1/2

Catalog Number	Type	Input Voltage AC	Мощность W	Number of Output Voltages	Voltage 1	Current 1
13105-004	19" Linear Regulator	230V	16W	1	24V	0.6A

CatalogNumber	Type	Input Voltage AC	Мощность W	Number of OutputVoltages	Voltage 1	Current 1
13105-003	19" Linear Regulator	230V	15W	1	15V	1A
13105-002	19" Linear Regulator	230V	13W	1	12V	1.1A
13105-001	19" Linear Regulator	230V	8W	1	5V	1.5A
13105-006	19" Linear Regulator	230V	20W	1	5V	4A
13105-013	19" Linear Regulator	230V	53W	1	15V	3.5A
13105-014	19" Linear Regulator	230V	60W	1	24V	2.5A
13105-012	19" Linear Regulator	230V	50W	1	12V	4.2A
13105-007	19" Linear Regulator	230V	31W	1	12V	2.8A
13105-011	19" Linear Regulator	230V	30W	1	5V	6A
13105-008	19" Linear Regulator	230V	33W	1	15V	2.2A
13105-009	19" Linear Regulator	230V	36W	1	24V	1.5A

Table 2/2						
Catalog Number	Rack Height	Rack Width	Глубина мм	Package Quantity	Certifications	Quick Ship
13105-004	3U	6HP	171.93mm	1	RoHS, CE, EN 62368-1	No
13105-003	3U	6HP	171.93mm	1	CE, EN 62368-1, RoHS	No
13105-002	3U	6HP	171.93mm	1	CE, EN 62368-1, RoHS	No
13105-001	3U	6HP	171.93mm	1	EN 62368-1, CE, RoHS	No
13105-006	3U	10HP	171.93mm	1	CE, RoHS	No

CatalogNumber	Rack Height	Rack Width	Глубина мм	Package Quantity	Certifications	Quick Ship
13105-013	3U	14HP	171.93mm	1	RoHS, CE	No
13105-014	3U	14HP	171.93mm	1	RoHS, CE	No
13105-012	3U	14HP	171.93mm	1	CE, RoHS	No
13105-007	3U	10HP	171.93mm	1	CE, RoHS	No
13105-011	3U	14HP	171.93mm	1	CE, RoHS	No
13105-008	3U	10HP	171.93mm	1	CE, RoHS	No
13105-009	3U	10HP	171.93mm	1	CE, RoHS	No

ADDITIONAL PRODUCT DETAILS

Передняя панель заказывается отдельно.

Выходные данные в Ta= 0 ... 50°C.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE