

19-дюймовый линейный регулятор переменного/постоянного тока для источника питания, Тройной

Линейный регулятор для вариантов применения, где требуется очень низкий уровень выходного шума.



CERTIFICATIONS



FEATURES

3 выходных напряжения, гальваническая развязка

Высокая точность управления, низкий уровень пульсаций и очень низкий уровень помех

Входное напряжение 230 В перем. тока (можно переключить на 115 В перем. тока с набором для преобразования входного напряжения)

Возможно применение в медицинском оборудовании (расстояние между токоведущими печатными проводниками 8 мм)

SPECIFICATIONS

Table 1/3

Catalog Number	Type	Input Voltage AC	Мощность W	Number of Output Voltages	Voltage 1	Current 1
13105-051	19" Linear Regulator	230V	8W	3	5V	0.5A

CatalogNumber	Type	Input Voltage AC	Мощность W	Number of OutputVoltages	Voltage 1	Current 1
13105-052	19" Linear Regulator	230V	20W	3	5V	1.5A
13105-053	19" Linear Regulator	230V	39W	3	5V	3A

Table 2/3

Catalog Number	Voltage 2	Current 2	Voltage 3	Current 3	Rack Height	Rack Width
13105-051	12V	0.2A	12V	0.2A	3U	6HP
13105-052	12V	0.5A	12V	0.5A	3U	10HP
13105-053	12V	1A	12V	1A	3U	14HP

Table 3/3

Catalog Number	Глубина мм	Package Quantity	Certifications	Quick Ship
13105-051	171.93mm	1	CE, EN 62368-1, RoHS	No
13105-052	171.93mm	1	CE, RoHS	No
13105-053	171.93mm	1	CE, RoHS	No

ADDITIONAL PRODUCT DETAILS

Передняя панель заказывается отдельно.

Выходные данные в Ta= 0 ... 50°C.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE