

19-дюймовый источник питания перем. тока/пост. тока Maxpower, 180 Вт, одинарный



Pluggable 19" Power Supplies with H15 connector for fanless applications. С широким диапазоном входного напряжения (переменный ток) и одним выходным напряжением.

CERTIFICATIONS



FEATURES

Широкий диапазон входного напряжения: 90 ... 254 В перем. тока и 100 ... 360 В пост. тока с активной коррекцией коэффициента мощности (PFC)

1 выходное напряжение

Сигнал "Выходное напряжение ОК"

КПД до 87 %

Встроенный развязывающий диод для операции резервирования

Равномерное распределение тока в параллельном режиме работы (CSB)

SPECIFICATIONS

Table 1/2

Catalog Number	Type	Input Voltage AC	Мощность W	Number of Output Voltages	Voltage 1	Current 1
----------------	------	------------------	------------	---------------------------	-----------	-----------

13100-152	19" Switched-Mode	90 – 264V	165W	1	15V	11A
13100-151	19" Switched-Mode	90 – 264V	156W	1	12V	13A
13100-150	19" Switched-Mode	90 – 264V	150W	1	5V	30A
13100-153	19" Switched-Mode	90 – 264V	168W	1	24V	7A

Table 2/2

Catalog Number	Rack Height	Rack Width	Package Quantity	Quick Ship
13100-152	3U	8HP	1	No
13100-151	3U	8HP	1	No
13100-150	3U	8HP	1	No
13100-153	3U	8HP	1	No

ADDITIONAL PRODUCT DETAILS

Передняя панель заказывается отдельно.

Выходные данные для напряжения сети > 190 В перем. тока, TA = 0 ... 50 °C.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE