

19-дюймовый корпус для монтажа в шкаф RatiopacPRO, Retrofittable Shielding



Корпус nVent SCHROFF RatiopacPRO обеспечивает защиту электроники для установки в 19-дюймовых решениях и отдельных сборках. Гибкий в установке и надежный корпус легко преобразуется из настольного решения в решение для установки в 19-дюймовый шкаф и поддерживает четыре варианта исполнения. В этом варианте корпуса предусмотрены монтажные кронштейны для установки в 19-дюймовый шкаф.

CERTIFICATIONS



FEATURES

Корпуса для индивидуальной сборки с 19" стандартными компонентами или особым внутренним креплением, например, на монтажной панели

Предназначен для ручек устройств для извлечения/вставки в соответствии с IEC 60297-3-102 и IEEE 1101.10 для систем CompactPCI и VME64x

Возможность дооснащения ЭМС-экранирования

Вариант с 19" монтажными кронштейнами

Для плат глубиной 160 мм, 220 мм, 280 мм, 340 мм (в зависимости от глубины корпуса)

Симметричная конструкция, идентичные передняя и задняя стороны

Нет видимых винтов, элементы оболочки снимаются без инструментов

В соответствии с DIN EN 62368-1

SPECIFICATIONS

Rack Width:	84HP
Product Type:	Корпус
Type:	Case for Individual Electronic Components

EMC Shielding: No (Retrofittable)

Product Family: RatiopacPRO

Table 1/3

Catalog Number	Rack Height	Глубина мм	Package Quantity	Usable Height	Usable Width	Front Frame Construction
24571-438	3U	255.5mm	1	112.3mm	432mm	19" Mounting Brackets, Horizontal Rails
24571-441	3U	315.5mm	1	112.3mm	432mm	19" Mounting Brackets, Horizontal Rails
24571-442	3U	375.5mm	1	112.3mm	432mm	19" Mounting Brackets, Horizontal Rails
24571-443	3U	435.5mm	1	112.3mm	432mm	19" Mounting Brackets, Horizontal Rails
24571-444	3U	495.5mm	1	112.3mm	432mm	19" Mounting Brackets, Horizontal Rails
24571-486	4U	255.5mm	1	156.8mm	432mm	19" Mounting Brackets, Horizontal Rails
24571-489	4U	315.5mm	1	156.8mm	432mm	19" Mounting Brackets, Horizontal Rails
24571-490	4U	375.5mm	1	156.8mm	432mm	19" Mounting Brackets, Horizontal Rails
24571-491	4U	435.5mm	1	156.8mm	432mm	19" Mounting Brackets, Horizontal Rails
24571-492	4U	495.5mm	1	156.8mm	432mm	19" Mounting Brackets, Horizontal Rails
24571-534	6U	255.5mm	1	245.7mm	432mm	19" Mounting Brackets, Horizontal Rails
24571-537	6U	315.5mm	1	245.7mm	432mm	19" Mounting Brackets, Horizontal Rails
24571-538	6U	375.5mm	1	245.7mm	432mm	19" Mounting Brackets, Horizontal Rails

CatalogNumber	Rack Height	Глубина мм	Package Quantity	Usable Height	Usable Width	Front Frame Construction
24571-539	6U	435.5mm	1	245.7mm	432mm	19" Mounting Brackets, Horizontal Rails
24571-540	6U	495.5mm	1	245.7mm	432mm	19" Mounting Brackets, Horizontal Rails
24572-201	5U	255.5mm	1	201.25mm	432mm	19" Mounting Brackets, Horizontal Rails
24572-204	5U	315.5mm	1	201.25mm	432mm	19" Mounting Brackets, Horizontal Rails
24572-205	5U	375.5mm	1	201.25mm	432mm	19" Mounting Brackets, Horizontal Rails
24572-206	5U	435.5mm	1	201.25mm	432mm	19" Mounting Brackets, Horizontal Rails
24572-207	5U	495.5mm	1	201.25mm	432mm	19" Mounting Brackets, Horizontal Rails
24572-345	5U	255.5mm	1	201.25mm	432mm	19" Mounting Brackets, Horizontal Rails
24572-348	5U	315.5mm	1	201.25mm	432mm	19" Mounting Brackets, Horizontal Rails
24572-349	5U	375.5mm	1	201.25mm	432mm	19" Mounting Brackets, Horizontal Rails
24572-350	5U	435.5mm	1	201.25mm	432mm	19" Mounting Brackets, Horizontal Rails
24572-351	5U	495.5mm	1	201.25mm	432mm	19" Mounting Brackets, Horizontal Rails
24572-570	2U	255.5mm	1	67.9mm	432mm	19" Mounting Brackets, Horizontal Rails
24572-573	2U	315.5mm	1	67.9mm	432mm	19" Mounting Brackets, Horizontal Rails

CatalogNumber	Rack Height	Глубина мм	Package Quantity	Usable Height	Usable Width	Front Frame Construction
24572-574	2U	375.5mm	1	67.9mm	432mm	19" Mounting Brackets, Horizontal Rails
24572-575	2U	435.5mm	1	67.9mm	432mm	19" Mounting Brackets, Horizontal Rails
24572-576	2U	495.5mm	1	67.9mm	432mm	19" Mounting Brackets, Horizontal Rails

Table 2/3

Catalog Number	Cooling Option	Complies With	Finish	Высота мм	Material	Protection Rating
24571-438	Нет	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Powder Coated	132.6mm	Алюминий	IP20
24571-441	Нет	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Powder Coated	132.6mm	Алюминий	IP20
24571-442	Нет	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Powder Coated	132.6mm	Алюминий	IP20
24571-443	Нет	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Powder Coated	132.6mm	Алюминий	IP20
24571-444	Нет	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Powder Coated	132.6mm	Алюминий	IP20

CatalogNumber	Cooling Option	Complies With	Finish	Высота мм	Material	Protection Rating
24571-486	Нет	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Powder Coated	177mm	Алюминий	IP20
24571-489	Нет	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Powder Coated	177mm	Алюминий	IP20
24571-490	Нет	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Powder Coated	177mm	Алюминий	IP20
24571-491	Нет	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Powder Coated	177mm	Алюминий	IP20
24571-492	Нет	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Powder Coated	177mm	Алюминий	IP20
24571-534	Нет	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Powder Coated	265.9mm	Алюминий	IP20
24571-537	Нет	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Powder Coated	265.9mm	Алюминий	IP20

CatalogNumber	Cooling Option	Complies With	Finish	Высота мм	Material	Protection Rating
24571-538	Нет	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Powder Coated	265.9mm	Алюминий	IP20
24571-539	Нет	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Powder Coated	265.9mm	Алюминий	IP20
24571-540	Нет	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Powder Coated	265.9mm	Алюминий	IP20
24572-201	Нет	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Powder Coated	221.5mm	Алюминий	IP20
24572-204	Нет	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Powder Coated	221.5mm	Алюминий	IP20
24572-205	Нет	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Powder Coated	221.5mm	Алюминий	IP20
24572-206	Нет	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Powder Coated	221.5mm	Алюминий	IP20

CatalogNumber	Cooling Option	Complies With	Finish	Высота мм	Material	Protection Rating
24572-207	Нет	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Powder Coated	221.5mm	Алюминий	IP20
24572-345	Нет	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Powder Coated	221.5mm	Алюминий	IP20
24572-348	Нет	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Powder Coated	221.5mm	Алюминий	IP20
24572-349	Нет	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Powder Coated	221.5mm	Алюминий	IP20
24572-350	Нет	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Powder Coated	221.5mm	Алюминий	IP20
24572-351	Нет	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Powder Coated	221.5mm	Алюминий	IP20
24572-570	Нет	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Powder Coated	88.1mm	Алюминий	IP20

CatalogNumber	Cooling Option	Complies With	Finish	Высота мм	Material	Protection Rating
24572-573	Нет	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Powder Coated	88.1mm	Алюминий	IP20
24572-574	Нет	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Powder Coated	88.1mm	Алюминий	IP20
24572-575	Нет	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Powder Coated	88.1mm	Алюминий	IP20
24572-576	Нет	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Powder Coated	88.1mm	Алюминий	IP20

Table 3/3

Catalog Number	Static Load	Ширина мм	Quick Ship
24571-438	25kg	448.9mm	No
24571-441	25kg	448.9mm	No
24571-442	25kg	448.9mm	No
24571-443	25kg	448.9mm	No
24571-444	25kg	448.9mm	No
24571-486	25kg	448.9mm	No
24571-489	25kg	448.9mm	No

Catalog Number	Static Load	Ширина мм	Quick Ship
24571-490	25kg	448.9mm	No
24571-491	25kg	448.9mm	No
24571-492	25kg	448.9mm	No
24571-534	25kg	448.9mm	No
24571-537	25kg	448.9mm	No
24571-538	25kg	448.9mm	No
24571-539	25kg	448.9mm	No
24571-540	25kg	448.9mm	No
24572-201	25kg	448.9mm	No
24572-204	25kg	448.9mm	No
24572-205	25kg	448.9mm	No
24572-206	25kg	448.9mm	No
24572-207	25kg	448.9mm	No
24572-345	25kg	448.9mm	No
24572-348	25kg	448.9mm	No
24572-349	25kg	448.9mm	No
24572-350	25kg	448.9mm	No
24572-351	25kg	448.9mm	No

Catalog Number	Static Load	Ширина мм	Quick Ship
24572-570	25kg	448.9mm	No
24572-573	25kg	448.9mm	No
24572-574	25kg	448.9mm	No
24572-575	25kg	448.9mm	No
24572-576	25kg	448.9mm	No

ADDITIONAL PRODUCT DETAILS

Модификации (специальные цвета или размеры).

Индивидуальные решения (вырезы в верхней крышке, панели основания или боковых панелях).

Услуга сборки при заказе от 1 шт.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE