

панель электропитания, UTE, с входом Wieland®



Компактная модульная конструкция панели электропитания с множеством функциональных элементов. Эта панель электропитания с алюминиевым шасси размером 1 U x 1 U легко интегрируется в шкаф. Разъем Wieland обеспечивает простую комбинацию с различными входными кабелями питания.

CERTIFICATIONS



FEATURES

Вход: штекер Wieland® GST 18

Во время установки панель электропитания можно поворачивать во всех направлениях (с шагом 90°)

Выход: розетки UTE

Горизонтальная или вертикальная установка

Установочная высота 1 U

В соответствии с NFC 61-303

Монтажная высота 1 U

В соответствии с NFC 61-303

SPECIFICATIONS

Длина мм:	438.5mm
Material:	Алюминий; Polyamide
Product Type:	Панели электропитания

Table 1/2

Catalog Number	Socket Type	Socket Quantity	Switched Outlets	Voltage AC	Function	Package Quantity
60110-357	UTE	6	Нет	230V	Overcurrent Protection	1
60110-356	UTE	6	Нет	230V	Overcurrent Protection	1
60110-346	UTE	8	Нет	230V		1
60110-355	UTE	6	Нет	230V	Overcurrent Protection	1
60110-348	UTE	8	Нет	230V		1
60110-347	UTE	8	Нет	230V		1

Table 2/2

Catalog Number	Color	Глубина мм	Finish	Quick Ship
60110-357	Красный	44mm	Anodized	No
60110-356	Черный	44mm	Anodized	No
60110-346	White	44mm	Anodized	No
60110-355	White	44mm	Anodized	No
60110-348	Красный	44mm	Anodized	No
60110-347	Черный	44mm	Anodized	No

ADDITIONAL PRODUCT DETAILS

Кронштейн для вертикального монтажа заказывается отдельно.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE