


Varistar CP Base Plate With Cable Entry

Varistar CP Base Plate for Rear Cable Ducting, plain for IP 55 or EMC applications.



FEATURES

Installation from outside

Cutout at rear

60 mm deep

Cable ducting with IP 55 / EMC gasket

SPECIFICATIONS

Product Type: Cabinet/Rack Base

Material: Сталь

Table 1/2

Catalog Number	Ширина мм	Глубина мм	Protection Rating	Package Quantity	Color	Color Code
21630-642	600mm	600mm		1		
21630-643	600mm	800mm		1		
21630-648	800mm	600mm		1		
21630-649	800mm	800mm		1		
21630-644	600mm	900mm		1		

CatalogNumber	Ширина мм	Глубина мм	Protection Rating	Package Quantity	Color	Color Code
21630-645	600mm	1000mm		1		
21630-650	800mm	900mm		1		
21630-651	800mm	1000mm		1		
21630-646	600mm	1100mm		1		
21630-647	600mm	1200mm		1		
21630-652	800mm	1100mm		1		
21630-653	800mm	1200mm		1		
21630-698	600mm	300mm		1	Black Grey	RAL 7021
21630-699	600mm	600mm		1	Black Grey	RAL 7021
21630-700	600mm	800mm		1	Black Grey	RAL 7021
21630-701	600mm	900mm		1	Black Grey	RAL 7021
21630-702	600mm	1000mm		1	Black Grey	RAL 7021
21630-703	600mm	1100mm		1	Black Grey	RAL 7021
21630-704	600mm	1200mm		1	Black Grey	RAL 7021
21630-705	800mm	600mm		1	Black Grey	RAL 7021
21630-706	800mm	800mm		1	Black Grey	RAL 7021
21630-707	800mm	900mm		1	Black Grey	RAL 7021
21630-708	800mm	1000mm		1	Black Grey	RAL 7021

CatalogNumber	Ширина мм	Глубина мм	Protection Rating	Package Quantity	Color	Color Code
21630-709	800mm	1100mm		1	Black Grey	RAL 7021
21630-710	800mm	1200mm		1	Black Grey	RAL 7021
21630-826	600mm	600mm	IP20	1		
21630-827	600mm	800mm	IP20	1		
21630-828	600mm	900mm	IP20	1		
21630-829	600mm	1000mm	IP20	1		
21630-830	600mm	1100mm	IP20	1		
21630-831	600mm	1200mm	IP20	1		
21630-832	800mm	600mm	IP20	1		
21630-833	800mm	800mm	IP20	1		
21630-834	800mm	900mm	IP20	1		
21630-835	800mm	1000mm		1		
21630-836	800mm	1100mm	IP20	1		
21630-837	800mm	1200mm	IP20	1		

Table 2/2

Catalog Number	Complies With	Finish	Works With	Quick Ship
21630-642		Hot-Dip Galvanized		No
21630-643		Hot-Dip Galvanized		No
21630-648		Hot-Dip Galvanized		No

Catalog Number	Complies With	Finish	Works With	Quick Ship
21630-649		Hot-Dip Galvanized		No
21630-644		Hot-Dip Galvanized		No
21630-645		Hot-Dip Galvanized		No
21630-650		Hot-Dip Galvanized		No
21630-651		Hot-Dip Galvanized		No
21630-646		Hot-Dip Galvanized		No
21630-647		Hot-Dip Galvanized		No
21630-652		Hot-Dip Galvanized		No
21630-653		Hot-Dip Galvanized		No
21630-698				No
21630-699				No
21630-700				No
21630-701				No
21630-702				No
21630-703				No
21630-704				No
21630-705				No
21630-706				No

Catalog Number	Complies With	Finish	Works With	Quick Ship
21630-707				No
21630-708				No
21630-709				No
21630-710				No
21630-826	IEC 61587-1, IEC 61587-3	Hot-Dip Galvanized	Varistar CP	No
21630-827	IEC 61587-1, IEC 61587-3	Hot-Dip Galvanized	Varistar CP	No
21630-828	IEC 61587-1, IEC 61587-3	Hot-Dip Galvanized	Varistar CP	No
21630-829	IEC 61587-1, IEC 61587-3	Hot-Dip Galvanized	Varistar CP	No
21630-830	IEC 61587-1, IEC 61587-3	Hot-Dip Galvanized	Varistar CP	No
21630-831	IEC 61587-1, IEC 61587-3	Hot-Dip Galvanized	Varistar CP	No
21630-832	IEC 61587-1, IEC 61587-3	Hot-Dip Galvanized	Varistar CP	No
21630-833	IEC 61587-1, IEC 61587-3	Hot-Dip Galvanized	Varistar CP	No
21630-834	IEC 61587-1, IEC 61587-3	Hot-Dip Galvanized	Varistar CP	No
21630-835	IEC 61587-1, IEC 61587-3	Hot-Dip Galvanized	Varistar CP	No
21630-836	IEC 61587-1, IEC 61587-3	Hot-Dip Galvanized	Varistar CP	No
21630-837	IEC 61587-1, IEC 61587-3	Hot-Dip Galvanized	Varistar CP	No

ADDITIONAL PRODUCT DETAILS

Varistar CP Base Plate for Rear Cable Ducting, plain for IP 55 or EMC applications.

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE