

Varistar CP Base/Plinth Side

Боковая планка для крепления к цоколю Varistar CP



FEATURES

Боковые стороны цоколя, сплошная

SPECIFICATIONS

Product Type: Cabinet/Rack Base

Material: Сталь

Table 1/2

Catalog Number	Высота мм	Глубина мм	Package Quantity	Color	Color Code	Finish
24630-083	100mm	300mm	1	Black Grey	RAL 7021	Powder Coated
24630-084	200mm	300mm	1	Black Grey	RAL 7021	Powder Coated
24630-077	100mm	600mm	1	Black Grey	RAL 7021	Powder Coated
24630-080	200mm	600mm	1	Black Grey	RAL 7021	Powder Coated
24630-078	100mm	800mm	1	Black Grey	RAL 7021	Powder Coated
24630-081	200mm	800mm	1	Black Grey	RAL 7021	Powder Coated
24630-079	100mm	900mm	1	Black Grey	RAL 7021	Powder Coated

CatalogNumber	Высота мм	Глубина мм	Package Quantity	Color	Color Code	Finish
24630-082	200mm	900mm	1	Black Grey	RAL 7021	Powder Coated
24630-038	100mm	1000mm	1	Black Grey	RAL 7021	Powder Coated
24630-041	200mm	1000mm	1	Black Grey	RAL 7021	Powder Coated
24630-039	100mm	1100mm	1	Black Grey	RAL 7021	Powder Coated
24630-042	200mm	1100mm	1	Black Grey	RAL 7021	Powder Coated
24630-040	100mm	1200mm	1	Black Grey	RAL 7021	Powder Coated
24630-043	200mm	1200mm	1	Black Grey	RAL 7021	Powder Coated

Table 2/2

Catalog Number	Type	Package Unit	Quick Ship
24630-083	Plinth Side		No
24630-084	Plinth Side		No
24630-077	Plinth Side	Pair	No
24630-080	Plinth Side	Pair	No
24630-078	Plinth Side	Pair	No
24630-081	Plinth Side	Pair	No
24630-079	Plinth Side	Pair	No
24630-082	Plinth Side	Pair	No
24630-038	Plinth Side	Pair	No
24630-041	Plinth Side	Pair	No

Catalog Number	Type	Package Unit	Quick Ship
24630-039	Plinth Side	Pair	No
24630-042	Plinth Side	Pair	No
24630-040	Plinth Side	Pair	No
24630-043	Plinth Side	Pair	No

ADDITIONAL PRODUCT DETAILS

Цоколь для передней/задней части следует заказывать отдельно.

Не используется в комбинации с поворотными роликами

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE