

Varistar CP EMC Shortened Rear Panel with Recessed Mounting Plate



Recessed connection plates are needed for connectors which don't protrude out of the plane of the cabinet

FEATURES

Intelligent cable management design with recessed connection plates

Connection plate is 400 mm high

For recessed plate: Plate recessed by 40 mm

SPECIFICATIONS

Product Type:	Cabinet/Rack Panel
Protection Rating:	IP55
Material:	Сталь; Stainless Сталь

Table 1/1

Catalog Number	Rack Height	Высота мм	Ширина мм	Package Quantity	Finish	Quick Ship
21630-911	42U	2000mm	600mm	1	Powder Coated	No
21630-909	38U	1800mm	600mm	1	Powder Coated	No
21630-914	47U	2200mm	800mm	1	Powder Coated	No
21630-910	38U	1800mm	800mm	1	Powder Coated	No

CatalogNumber	Rack Height	Высота мм	Ширина мм	Package Quantity	Finish	Quick Ship
21630-913	47U	2200mm	600mm	1	Powder Coated	No
21630-912	42U	2000mm	800mm	1	Powder Coated	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE