

Varistar CP Plain Steel Door, Seismic IP55, With Multi-Point Locking



IP55 Seismic Steel Door with lever handle and multi-Point locking.

FEATURES

Lever handle with push button

Opening angle 180°

Steel door with Multi-Point locking for EMC applications

SPECIFICATIONS

Product Type: Cabinet Door

Protection Rating: IP55

Material: Сталь

Table 1/3

Catalog Number	Rack Height	Высота мм	Ширина мм	Package Quantity	Color	Color Code
21630-752	33U	1600mm	600mm	1	Black Grey	RAL 7021
21630-753	33U	1600mm	800mm	1	Black Grey	RAL 7021
21630-754	38U	600mm	600mm	1	Black Grey	RAL 7021
21630-755	38U	1800mm	800mm	1	Black Grey	RAL 7021

CatalogNumber	Rack Height	Высота мм	Ширина мм	Package Quantity	Color	Color Code
21630-756	42U	2000mm	600mm	1	Black Grey	RAL 7021
21630-757	42U	2000mm	800mm	1	Black Grey	RAL 7021
21630-758	47U	2200mm	600mm	1	Black Grey	RAL 7021
21630-759	47U	2200mm	800mm	1	Black Grey	RAL 7021

Table 2/3						
Catalog Number	Complies With	Finish	Locking Type	Rack Width	Type	Works With
21630-752	IEC 61587-1, IEC 61587-2, IEC 60529	Powder Coated	4-Point Locking		Сплошная стальная дверь	Varistar CP
21630-753	IEC 61587-1, IEC 61587-2, IEC 60529	Powder Coated	4-Point Locking	800HP	Сплошная стальная дверь	Varistar CP
21630-754	IEC 61587-2, IEC 61587-2, IEC 60529	Powder Coated	4-Point Locking		Сплошная стальная дверь	Varistar CP
21630-755	IEC 61587-1, IEC 61587-2, IEC 60529	Powder Coated	4-Point Locking		Сплошная стальная дверь	Varistar CP
21630-756	IEC 61587-1, IEC 61587-2, IEC 60529	Powder Coated	4-Point Locking		Сплошная стальная дверь	Varistar CP
21630-757	IEC 61587-1, IEC 61587-2, IEC 60529	Powder Coated	4-Point Locking		Сплошная стальная дверь	Varistar CP
21630-758	IEC 61587-1, IEC 61587-2, IEC 60529	Powder Coated	5-Point Locking		Сплошная стальная дверь	Varistar CP
21630-759	IEC 61587-1, IEC 61587-2, IEC 60529	Powder Coated	5-Point Locking		Сплошная стальная дверь	Varistar CP

Table 3/3	
Catalog Number	Quick Ship
21630-752	No

Catalog Number	Quick Ship
21630-753	No
21630-754	No
21630-755	No
21630-756	No
21630-757	No
21630-758	No
21630-759	No

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE