

# Varistar CP Top Cover With Fan Tray



Varistar Fan Top Cover with 3 Fans, expandable to 6 fans.

## FEATURES

6 axial fans fitted

Schuko/IEC 60320 C12 plug

6 power saving axial fans fitted

Wide range power input 90-260 VAC

Speed control with 2 T° sensors

Alarm over T° and fan fail ( Display panel at front & relay outputs)

Remote control over Modbus RTU or Guardian

SPECIFICATIONS

Product Type: Fan  
Material: Сталь

| Table 1/3      |           |            |                  |            |         |             |
|----------------|-----------|------------|------------------|------------|---------|-------------|
| Catalog Number | Ширина мм | Глубина мм | Package Quantity | Voltage DC | Airflow | Noise Level |
| 21630-777      | 600mm     | 600mm      | 1                | 24V        | 171m³/h | 42.5dB(A)   |
| 21630-778      | 600mm     | 800mm      | 1                | 24V        | 171m³/h | 42.5dB(A)   |
| 21630-783      | 800mm     | 600mm      | 1                | 24V        | 171m³/h | 42.5dB(A)   |
| 21630-784      | 800mm     | 800mm      | 1                | 24V        | 171m³/h | 42.5dB(A)   |
| 21630-785      | 800mm     | 900mm      | 1                | 24V        | 171m³/h | 42.5dB(A)   |
| 21630-786      | 800mm     | 1000mm     | 1                | 24V        | 171m³/h | 42.5dB(A)   |
| 21630-779      | 600mm     | 900mm      | 1                | 24V        | 171m³/h | 42.5dB(A)   |
| 21630-780      | 600mm     | 1000mm     | 1                | 24V        | 171m³/h | 42.5dB(A)   |
| 21630-781      | 600mm     | 1100mm     | 1                | 24V        | 171m³/h | 42.5dB(A)   |
| 21630-782      | 600mm     | 1200mm     | 1                | 24V        | 171m³/h | 42.5dB(A)   |
| 21630-787      | 800mm     | 1100mm     | 1                | 24V        | 171m³/h | 42.5dB(A)   |
| 21630-788      | 800mm     | 1200mm     | 1                | 24V        | 171m³/h | 42.5dB(A)   |
| 21630-790      | 600mm     | 600mm      | 1                | 24V        | 171m³/h | 42.5dB(A)   |
| 21630-791      | 600mm     | 800mm      | 1                | 24V        | 171m³/h | 42.5dB(A)   |
| 21630-792      | 600mm     | 900mm      | 1                | 24V        | 171m³/h | 42.5dB(A)   |
| 21630-793      | 600mm     | 1000mm     | 1                | 24V        | 171m³/h | 42.5dB(A)   |

| CatalogNumber | Ширина мм | Глубина мм | Package Quantity | Voltage DC | Airflow | Noise Level |
|---------------|-----------|------------|------------------|------------|---------|-------------|
| 21630-794     | 600mm     | 1100mm     | 1                | 24V        | 171m³/h | 42.5dB(A)   |
| 21630-795     | 600mm     | 1200mm     | 1                | 24V        | 171m³/h | 42.5dB(A)   |
| 21630-796     | 800mm     | 600mm      | 1                | 24V        | 171m³/h | 42.5dB(A)   |
| 21630-797     | 800mm     | 800mm      | 1                | 24V        | 171m³/h | 42.5dB(A)   |
| 21630-798     | 800mm     | 900mm      | 1                | 24V        | 171m³/h | 42.5dB(A)   |
| 21630-799     | 800mm     | 1000mm     | 1                | 24V        | 171m³/h | 42.5dB(A)   |
| 21630-800     | 800mm     | 1100mm     | 1                | 24V        | 171m³/h | 42.5dB(A)   |
| 21630-801     | 800mm     | 1200mm     | 1                | 24V        | 171m³/h | 42.5dB(A)   |

| Table 2/3      |                     |            |            |               |               |                   |
|----------------|---------------------|------------|------------|---------------|---------------|-------------------|
| Catalog Number | Max Static Pressure | Color      | Color Code | Complies With | Finish        | Protection Rating |
| 21630-777      | 68.1Pa              | Black Grey | RAL 7021   | IEC 61587-1   | Powder Coated | IP20              |
| 21630-778      | 68.1Pa              | Black Grey | RAL 7021   | IEC 61587-1   | Powder Coated | IP20              |
| 21630-783      | 68.1Pa              | Black Grey | RAL 7021   | IEC 61587-1   | Powder Coated | IP20              |
| 21630-784      | 68.1Pa              | Black Grey | RAL 7021   | IEC 61587-1   | Powder Coated | IP20              |
| 21630-785      | 68.1Pa              | Black Grey | RAL 7021   | IEC 61587-1   | Powder Coated | IP20              |
| 21630-786      | 68.1Pa              | Black Grey | RAL 7021   | IEC 61587-1   | Powder Coated | IP20              |
| 21630-779      | 68.1Pa              | Black Grey | RAL 7021   | IEC 61587-1   | Powder Coated | IP20              |
| 21630-780      | 68.1Pa              | Black Grey | RAL 7021   | IEC 61587-1   | Powder Coated | IP20              |

| CatalogNumber | Max Static Pressure | Color      | Color Code | Complies With | Finish        | Protection Rating |
|---------------|---------------------|------------|------------|---------------|---------------|-------------------|
| 21630-781     | 68.1Pa              | Black Grey | RAL 7021   | IEC 61587-1   | Powder Coated | IP20              |
| 21630-782     | 68.1Pa              | Black Grey | RAL 7021   | IEC 61587-1   | Powder Coated |                   |
| 21630-787     | 68.1Pa              | Black Grey | RAL 7021   | IEC 61587-1   | Powder Coated | IP20              |
| 21630-788     | 68.1Pa              | Black Grey | RAL 7021   | IEC 61587-1   | Powder Coated | IP20              |
| 21630-790     | 68.1Pa              | Black Grey | RAL 7021   | IEC 61587-1   | Powder Coated | IP20              |
| 21630-791     | 68.1Pa              | Black Grey | RAL 7021   | IEC 61587-1   | Powder Coated | IP20              |
| 21630-792     | 68.1Pa              | Black Grey | RAL 7021   | IEC 61587-1   | Powder Coated | IP20              |
| 21630-793     | 68.1Pa              | Black Grey | RAL 7021   | IEC 61587-1   | Powder Coated | IP20              |
| 21630-794     | 68.1Pa              | Black Grey | RAL 7021   | IEC 61587-1   | Powder Coated | IP20              |
| 21630-795     | 68.1Pa              | Black Grey | RAL 7021   | IEC 61587-1   | Powder Coated | IP20              |
| 21630-796     | 68.1Pa              | Black Grey | RAL 7021   | IEC 61587-1   | Powder Coated | IP20              |
| 21630-797     | 68.1Pa              | Black Grey | RAL 7021   | IEC 61587-1   | Powder Coated | IP20              |
| 21630-798     | 68.1Pa              | Black Grey | RAL 7021   | IEC 61587-1   | Powder Coated | IP20              |
| 21630-799     | 68.1Pa              | Black Grey | RAL 7021   | IEC 61587-1   | Powder Coated | IP20              |
| 21630-800     | 68.1Pa              | Black Grey | RAL 7021   | IEC 61587-1   | Powder Coated | IP20              |
| 21630-801     | 68.1Pa              | Black Grey | RAL 7021   | IEC 61587-1   | Powder Coated | IP20              |

Table 3/3

| Catalog Number | Type                 | Works With  | Quick Ship |
|----------------|----------------------|-------------|------------|
| 21630-777      | Крыша с вентилятором | Varistar CP | No         |

| Catalog Number | Type                 | Works With  | Quick Ship |
|----------------|----------------------|-------------|------------|
| 21630-778      | Крыша с вентилятором | Varistar CP | No         |
| 21630-783      | Крыша с вентилятором | Varistar CP | No         |
| 21630-784      | Крыша с вентилятором | Varistar CP | No         |
| 21630-785      | Крыша с вентилятором | Varistar CP | No         |
| 21630-786      | Крыша с вентилятором | Varistar CP | No         |
| 21630-779      | Крыша с вентилятором | Varistar CP | No         |
| 21630-780      | Крыша с вентилятором | Varistar CP | No         |
| 21630-781      | Крыша с вентилятором | Varistar CP | No         |
| 21630-782      | Крыша с вентилятором | Varistar CP | No         |
| 21630-787      | Крыша с вентилятором | Varistar CP | No         |
| 21630-788      | Крыша с вентилятором | Varistar CP | No         |
| 21630-790      | Крыша с вентилятором | Varistar CP | No         |
| 21630-791      | Крыша с вентилятором | Varistar CP | No         |
| 21630-792      | Крыша с вентилятором | Varistar CP | No         |
| 21630-793      | Крыша с вентилятором | Varistar CP | No         |
| 21630-794      | Крыша с вентилятором | Varistar CP | No         |
| 21630-795      | Крыша с вентилятором | Varistar CP | No         |
| 21630-796      | Крыша с вентилятором | Varistar CP | No         |

| Catalog Number | Type                 | Works With  | Quick Ship |
|----------------|----------------------|-------------|------------|
| 21630-797      | Крыша с вентилятором | Varistar CP | No         |
| 21630-798      | Крыша с вентилятором | Varistar CP | No         |
| 21630-799      | Крыша с вентилятором | Varistar CP | No         |
| 21630-800      | Крыша с вентилятором | Varistar CP | No         |
| 21630-801      | Крыша с вентилятором | Varistar CP | No         |

## ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**