

Система VPX, настольная, высота 4 U, 5 слотов, подключаемый источник питания



Настольный корпус TVPX для печатных плат 5 VPX 3 U, 160 мм. Опция расположения вводов-выводов на задней панели. Питание системы осуществляется от подключаемого бескорпусного источника питания.

CERTIFICATIONS



FEATURES

Объединительная плата соответствует VITA 46. Другие объединительные платы VPX по запросу. Система в соответствии с 60297IEC-3-101, 102-, 103-; IEEE 1101.1, 1101.10/11; объединительная плата в соответствии с VITA 1.1-1994

Подключаемый источник питания, 250 Вт, 3 U, 8 HP (дополнительный опциональный блок питания)

Объединительная плата VPX, соответствует требованиям VITA 46, 5 слота, 3 U, шаг 0,8 дюйм., топология полной сетки

Отвод тепла осуществляется 2 радиальными вентиляторами , охлаждение спереди назад

SPECIFICATIONS

Table 1/3

Catalog Number	Product Type	Number of Slots	Type	Backplane Type	Data Transfer	Power per Slot
20836-447	System	5	Настольный корпус	VPX Full Mesh	10 GbE	30W
20836-444	System	5	Настольный корпус	VPX Full Mesh	10 GbE	30W

Table 2/3

Catalog Number	Input Voltage AC	Airflow Direction	Rack Height	Power Supply Type	Power Supply Included	Rear I/O
20836-447	100 – 240V	Front to Rear	4U	(1) Pluggable PSU	Да	Да
20836-444	100 – 240V	Front to Rear	4U	(1) Pluggable PSU	Да	Нет

Table 3/3

Catalog Number	Complies With	Глубина мм	Высота мм	Package Quantity	Quick Ship
20836-447	ANSI/VITA 46.0-2019	275mm	177mm	1	No
20836-444	ANSI/VITA 46.0-2019	275mm	177mm	1	No

ADDITIONAL PRODUCT DETAILS

Модифицированные системы доступны по запросу.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE