

nVent CADDY Speed Link SLK with Hook, 1.5 mm Wire, 10 m Length

CATALOG NUMBER

SLK15L10



CERTIFICATIONS



FEATURES

Complete system includes wire, locking device and pre-assembled hook end fitting

Hooks to a wide range of nVent CADDY fasteners

Fastens to the building structure or hanging services by looping around and hooking to wire rope

Easy to remove for applications requiring maintenance

Spring latch helps provide secure connection

Insert cable through hole and use bottom side of hook as an end stop

Also available in Y-hook configuration

PRODUCT ATTRIBUTES

Article Number: 196513

Material: Сталь; Polypropylene; Zinc Alloy

Finish: Electrogalvanized

Static Load Safety Factor: 5:1

Wire Rope Diameter: 1.5 mm

Complies With: SMACNA HVAC-DCS

Wire Rope Length: 10m

A: 48 mm

B: 18 mm

C: 4.5 mm

Height (H): 55 mm

Width (W): 19 mm

Thickness (T): 12.5 mm

Angle (a): 90 ° Max

Static Load: 195N

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

