

H-MSS Inline Strap Hanger with Flange Clip



CERTIFICATIONS



FEATURES


Supports pipe or duct from flange with banding or strapping

SPECIFICATIONS

Table 1/1

Catalog Number	Article Number	Material	Finish	Flange Thickness (FT)	Strap Width	Static Load
MSS912	171770	Сталь, Spring Сталь	nVent CADDY Armour, Pregalvanized	14 - 20 mm	32 mm Max	900N

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

