

# nVent CADDY Cat HP J-Hook with Multi-Function Clip



## CERTIFICATIONS



## FEATURES

Quick attachment to threaded rod or wire

Fully adjustable and easy to relocate to accommodate changes once installed

Provides optimal support for high-performance data cable, up to and including Cat 5e, Cat 6, Cat 6A, Cat 7 and fibre optic

Provides superior fill capacity and load rating over most other non-continuous cable support alternatives

Rounded edges on J-Hooks provide proper bend radius support for high performance data cables

Cost effective alternative to expensive cable tray

Complies with EN 50174-2

Meets ISO®/IEC 14763-2, ANSI®/TIA 568 and ANSI®/TIA 569

Increased capability and application options by combining 4Z and 6Z products into one enhanced and efficient offering

Improved multi-function clip allows for optimized inventory while reducing job site scheduling risks associated with multiple SKUs

## SPECIFICATIONS

**Finish:** Pregalvanized;nVent CADDY Armour

**Material:** Сталь;Spring Сталь

Table 1/2

Catalog Number	Article Number	Diameter (Ø)	Area	Cable Capacity, Cat 5e	Cable Capacity, Cat 6	Cable Capacity, Cat 6A
CAT21HP4Z34	181258	33.3 mm	1174mm <sup>2</sup>	50	40	25
CAT32HP4Z34	181218	50 mm	2561mm <sup>2</sup>	90	60	35
CAT16HP4Z34	181217	25 mm	690mm <sup>2</sup>	20	15	10

Table 2/2


Catalog Number	Article Number	Wire Size	Rod Size (RS)	Static Load
CAT21HP4Z34	181258	3.9 - 4.8 mm	4, 6, 8, 10	130N
CAT32HP4Z34	181218	3.9 - 4.8 mm	4, 6, 8, 10	130N
CAT16HP4Z34	181217	3.9 - 4.8 mm	4, 6, 8, 10	130N

## ADDITIONAL PRODUCT DETAILS

Non-continuous supports may not exceed spacing of 5' (1.5 m) per TIA 569-C.9.7 and EN 50174-2.

Cable capacity is calculated based on a 70% fill rate.

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**

