

# Дверной контактный выключатель без кабеля

## Data Solutions



Дверной контактный выключатель с магнитным контактом обеспечивает эксплуатационную эффективность. Это изделие легко подключается по принципу «подключи и работай».

## CERTIFICATIONS



## FEATURES

Переключатель контактов двери (без соединительного кабеля)

## SPECIFICATIONS

Table 1/2

Catalog Number	Глубина мм	Высота мм	Operating Temperature	Protection Rating	Ширина мм	Complies With
20118-810	33.5mm	76.5mm	-25 to 75°C	IP66	31mm	UL® 508, EN 50047 form B

Table 2/2

Catalog Number	Current Rating	Package Quantity	Voltage	Wire Size
20118-810	3 – 6A	1	24 – 230V	0.5 – 2.5mm <sup>2</sup>

## ADDITIONAL PRODUCT DETAILS

---

Кронштейн для установки дверного выключателя (Varistar, Novastar, Eurorack) заказывается отдельно.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**