

Joint Bond T7 Complete Welder Pair, Signal

Data Solutions



FEATURES

Complete welder assembly provides a convenient means of attaching jumper bonds to the head of the rail, across the joint

Connection is made within the confines of the splice bar

Includes mold cleaner and flint ignitor

SPECIFICATIONS

Rail Type: 85 lb to 141 lb T-Rail Sections

Material: Сталь; Graphite

Table 1/1

Catalog Number	Bond Terminal Style	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style
SBHFT7E	Head Free	3/16" Bondstrand	4.76mm	T7
SBHFT7K	Head Free	5/16" Bondstrand	4.76mm	T7
SBTBT7F	3/4" Tab	3/16" Bondstrand	4.76mm	T7
SBTBT7G	1" Tab	3/16" Bondstrand	4.76mm	T7

Catalog Number	Bond Terminal Style	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style
SBXST7D	3/4" XS	3/16" Bondstrand	4.76mm	T7
SBTBT7B	1" Tab	5/16" Bondstrand	7.94mm	T7

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including diisononyl phthalate, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE